

WE-PD SMT SHIELDED POWER INDUCTOR



more details online

744 777 001	744 777 002	744 777 004	744 777 10	744 777 115	744 777 122	744 777 147
L: 1 μH R _{DC typ.} : 8.4 mΩ I _R : 6.84 A I _{SAT} : 10.2 A	L: 2.2 μH R _{DC typ.} : 13 mΩ I _R : 6 A I _{SAT} : 6.5 A	L: 4.7 μH R _{DC typ.} : 25 mΩ I _R : 3.2 A I _{SAT} : 4 A	L: 10 μH R _{DC typ.} : 45 mΩ I _R : 2 A I _{SAT} : 2.6 A	L: 15 μH R _{DC typ.} : 70 mΩ I _R : 1.6 A I _{SAT} : 2.2 A	L: 22 μH R _{DC typ.} : 90 mΩ I _R : 1.41 A I _{SAT} : 1.7 A	L: 47 μH R _{DC typ.} : 170 mΩ I _R : 1.03 A I _{SAT} : 1.1 A
						Robust
744 777 20	744 777 222	744 777 24	744 777 30			
L: 100 μH R _{DC typ.} : 290 mΩ I _R : 0.79 A I _{SAT} : 0.75 A	L: 220 μH R _{DC typ.} : 920 mΩ I _R : 0.44 A I _{SAT} : 0.54 A	L: 470 μH R _{DC typ.} : 1600 mΩ I _R : 0.29 A I _{SAT} : 0.34 A	L: 1000 μH R _{DC typ.} : 3270 mΩ I _R : 0.2 A I _{SAT} : 0.25 A			
Robust						
744 777 900 4	744 777 910	744 777 911 5	744 777 912 2	744 777 914 7	744 777 920	744 777 922 2
L: 4.7 μH R _{DC typ.} : 28 mΩ I _R : 3.16 A I _{SAT} : 4.4 A	L: 10 μH R _{DC typ.} : 45 mΩ I _R : 2 A I _{SAT} : 2.6 A	L: 15 μH R _{DC typ.} : 70 mΩ I _R : 1.6 A I _{SAT} : 2.2 A	L: 22 μH R _{DC typ.} : 90 mΩ I _R : 1.41 A I _{SAT} : 1.7 A	L: 47 μH R _{DC typ.} : 190 mΩ I _R : 1.03 A I _{SAT} : 1.1 A	L: 100 μH R _{DC typ.} : 290 mΩ I _R : 0.79 A I _{SAT} : 0.75 A	L: 220 μH R _{DC typ.} : 920 mΩ I _R : 0.44 A I _{SAT} : 0.54 A
Robust			Performance			
744 777 924	744 777 930					
L: 470 μH R _{DC typ.} : 1600 mΩ I _R : 0.29 A I _{SAT} : 0.34 A	L: 1000 μH R _{DC typ.} : 3270 mΩ I _R : 0.2 A I _{SAT} : 0.25 A					
Performance						
744 777 301 0	744 777 302 2	744 777 304 7	744 777 310 0			
L: 1 μH R _{DC typ.} : 8.4 mΩ I _R : 6 A I _{SAT} : 10 A	L: 2.2 μH R _{DC typ.} : 12.5 mΩ I _R : 4.8 A I _{SAT} : 8 A	L: 4.7 μH R _{DC typ.} : 20 mΩ I _R : 3.6 A I _{SAT} : 5.5 A	L: 10 μH R _{DC typ.} : 37.5 mΩ I _R : 2.6 A I _{SAT} : 3.8 A			
Performance						
744 777 315 0	744 777 322 0	744 777 347 0	744 777 310 1	744 777 322 1	744 777 347 1	744 777 310 2
L: 15 μH R _{DC typ.} : 53 mΩ I _R : 2.2 A I _{SAT} : 3.1 A	L: 22 μH R _{DC typ.} : 75 mΩ I _R : 1.85 A I _{SAT} : 2.5 A	L: 47 μH R _{DC typ.} : 150 mΩ I _R : 1.3 A I _{SAT} : 1.7 A	L: 100 μH R _{DC typ.} : 270 mΩ I _R : 0.97 A I _{SAT} : 1.2 A	L: 220 μH R _{DC typ.} : 640 mΩ I _R : 0.63 A I _{SAT} : 0.81 A	L: 470 μH R _{DC typ.} : 1360 mΩ I _R : 0.43 A I _{SAT} : 0.55 A	L: 1000 μH R _{DC typ.} : 2850 mΩ I _R : 0.3 A I _{SAT} : 0.38 A