	1		2		3	4	5	
		After assembly	2.54		LAST - PIN - PIN - PIN 	TECHNICAL CHARACTI MATERIAL INSULATOR: PBT COLOR: GREY CONTACT MATERIAL: (CONTACT TYPE: STAM CONTACT PLATING: SE QUALITY CLASS: 3 AS PITCH: 2.54MM ENVIRONMENTAL OPERATING TEMPERA FLAMABILITY RATING: COMPLIANCE: LEAD FI ELECTRICAL CURRENT RATING: 1A WORKING VOLTAGE: 2 INSULATOR RESISTAN	ERISTICS COPPER ALLOY PED ELECTIVE GOLD PER CECC 75 301-802 TURE: -40 UP TO 125°C UL94-V0 REE AND ROHS MAX 50V AC CE: >1000 MOHM NDING VOLTAGE: 500V AC/MN E: 20 mOHM MAX 1) + 5.30	
G R	oHS Compliant			PROJECTION:	GENERAL TOLERANCE	- -		
-				1	.X = ⁺ /_ 0.2			
=					.XX = ⁺ /_ 0.15			
)	26-DEC-07	PIN POS. / SOLDER.	СН					
_	19-DEC-06	DRAW	EC	APPROVAL: RJ	UNIT: MM	DESCRIPTION: 2.54MM MALE IDC CONNECTO	OR SIZE	
		LEAD FREE	JP		SCALE:			-
	29-MAR-04							
C B A	29-MAR-04 31-JAN-01	PDF	JP		SHEET: 1/1	WERI PART NO: 6120 xx 25821	A4	4