

1

2

3

4

5

TECHNICAL CHARACTERISTICS

MATERIAL
COLOR: BLACK
STYLE: UL1007

ENVIRONMENTAL
OPERATING TEMPERATURE: -20°C UP TO 80°C
COMPLIANCE: LEAD FREE AND ROHS

WIRE DIMENSION
AWG: 20

PACKAGING
10 PCS/BAG

A

B

C

Terminal A



Terminal B

Wire Length 300mm

Terminal A	662 003 137 22
Terminal B	662 003 137 22

RoHS Compliant

G			
F			
E			
D			
C			
B			
A	30-APR-12	PDF	GG
REV	DATE	FILE	BY

PROJECTION:

GENERAL TOLERANCE
.X = +/- 0.2
.XX = +/- 0.15



APPROVAL: RJ

UNIT: MM
SCALE:
SHEET: 1/2
DRAW: QL

DESCRIPTION: WR-MPC3 FEMALE LOW FORCE PRE-CRIMPED CABLE
WERI PART NO: 662 362 320 030

SIZE
A4

D

1

2

3

4

5

A

B

C

D

Note:
 1.Dimension
 Carton Size:40*30*20(CM)
 2.Quantity: 5000 Pcs/Carton



RoHS Compliant

G			
F			
E			
D			
C			
B			
A			
REV	DATE	FILE	BY

PROJECTION:

GENERAL TOLERANCE
 .X = +/- 0.2
 .XX = +/- 0.15



APPROVAL: RJ

UNIT: MM
 SCALE:
 SHEET: 2/2
 DRAW: QL

DESCRIPTION: WR-MPC3 FEMALE LOW FORCE PRE-CRIMPED CABLE
 WERI PART NO: 662 362 120 030

SIZE
A4