

1

2

3

4

5


CHARACTERISTICS:

MATERIAL:
COLOR: BLACK
OPERATING TEMPERATURE: -20°C UP TO 80°C
COMPLIANCE: LEAD FREE AND ROHS

PACKAGING:
10PCS/BAG

WIRE DIMENSION:
AWG: 24

Terminal A





3mm Pre-stripped

Terminal B

Wire Length 150mm*

Terminal A	649 009 137 22
Terminal B	Pre-stripped

* Note: Wire UL 1007

RoHS Compliant				PROJECTION:	GENERAL TOLERANCE		DESCRIPTION: WR-MPC4 MALE PRE-CRIMPED CONTACT WERI PART NO: 649 900 124 015	SIZE A4
G					.X = +/- 0.2			
F					APPROVAL: RJ	.XX = +/- 0.15	UNIT: MM	
E						SCALE:		
D						SHEET: 1/2		
C						DRAW: QL		
B								
A	18-OCT-11	PDF	GG					
REV	DATE	FILE	BY					

1

2

3

4

5


A

B

C

D

Note:
 1.Dimension
 Carton Size:40*30*20(CM)
 2.Quantity: 5000 Pcs/Carton



RoHS Compliant

G			
F			
E			
D			
C			
B			
A			
REV	DATE	FILE	BY

PROJECTION:

APPROVAL: RJ

GENERAL TOLERANCE
 .X = +/- 0.2
 .XX = +/- 0.15

UNIT: MM
 SCALE:
 SHEET: 2/2
 DRAW: QL



DESCRIPTION: WR-MPC4 MALE PRE-CRIMPED CONTACT
 WERI PART NO: 649 900 124 015

SIZE
A4