




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



**ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	8-2 @20°C	0.135 ohms ±10%
INDUCTANCE	8-2 100kHz, 1.0V, Ls	300µH ±5%
DIELECTRIC	8-core 625VAC, 1 second	500VAC, 1 minute



RECOMMENDED P.C. PATTERN, COMPONENT SIDE

**GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety standard undefined.

UL Recognized Class B insulation system M1-130(B), E106391.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	SP	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1°    Decimals: ±.005 [.13] Fractions: ±1/64    Footprint: ±.001 [.03]	DRAWING TITLE  <b>INDUCTOR</b>	PART NO.  <b>750315757</b>
DATE	10/15/2015	Method: Tray				
ENG	EJK	PKG-0103				
REV.	00					
DATE	11/5/2015	www.we-online.com/midcom				