

# WR-MCX PCB & CABLE CONNECTORS



more details online

<b>606 130 031 215 01</b>	<b>606 110 021 115 01</b>	<b>606 110 021 115 02</b>	<b>606 111 021 113 03</b>	<b>606 122 021 113 07</b>	<b>606 124 321 115 12</b>
THT	THT	THT	SMT	SMT	Panel (Front Mount)
Right Angle Plug	Right Angle Jack	Right Angle Jack	Right Angle Jack	End launch Jack	Bulkhead Jack
Center contact: $\varnothing$ 0.96 mm	Center contact: $\varnothing$ 0.96 mm	Center contact: $\varnothing$ 0.96 mm	Center contact: $\varnothing$ 0.96 mm	Center contact: $\varnothing$ 0.96 mm	Center contact: $\varnothing$ 1.45 mm
<b>606 140 031 215 04</b>	<b>606 120 021 115 04</b>	<b>606 120 021 115 05</b>	<b>606 121 021 114 06</b>	<b>606 122 021 113 08</b>	<b>606 127 021 115 13</b>
THT	THT	THT	SMT	SMT	Panel (Press In)
Straight Plug	Straight Jack	Straight Jack	Straight Jack	End launch Jack	Straight Jack
Center contact: $\varnothing$ 0.96 mm	Center contact: $\varnothing$ 0.96 mm	Center contact: $\varnothing$ 0.96 mm	Center contact: $\varnothing$ 0.96 mm	Center contact: $\varnothing$ 0.96 mm	Center contact: $\varnothing$ 1.2 mm
<b>606 460 312 104 20</b>	<b>606 460 312 103 20</b>	<b>606 460 312 106 20</b>	<b>606 490 312 108 20</b>	<b>606 122 021 113 09</b>	
RG178, 196	RG174, 316, 188	RG316 Double Braid	Hand Formable RG405 (.085)	SMT	
Straight Plug	Straight Plug	Straight Plug	Straight Plug	End launch Jack	
Ferrule Hex. :128°	Ferrule Hex. :128°	Ferrule Hex. :151°	Solder	Center contact: $\varnothing$ 0.5 mm	
<b>606 360 312 104 20</b>	<b>606 360 312 103 20</b>	<b>606 360 312 106 20</b>	<b>606 390 312 108 20</b>	<b>606 122 021 115 10</b>	
RG178, 196	RG174, 316, 188	RG316 Double Braid	Hand Formable RG405 (.085)	PCB 1.1 mm	
Right Angle Plug	Right Angle Plug	Right Angle Plug	Right Angle Plug	End launch Jack	
Ferrule Hex. :128°	Ferrule Hex. :128°	Ferrule Hex. :128°	Solder	Center contact: $\varnothing$ 0.48 mm	
<b>606 260 211 104 20</b>	<b>606 260 211 103 20</b>	<b>606 260 211 106 20</b>	<b>606 290 211 108 20</b>	<b>606 122 021 115 11</b>	
RG178, 196	RG174, 316, 188	RG316 Double Braid	Hand Formable RG405 (.085)	PCB 1.6 mm	
Straight Jack	Straight Jack	Straight Jack	Straight Jack	End launch Jack	
Ferrule Hex. :128°	Ferrule Hex. :128°	Ferrule Hex. :151°	Solder	Center contact: $\varnothing$ 0.48 mm	
<b>606 264 211 104 20</b>	<b>606 264 211 103 20</b>	<b>606 264 211 106 20</b>	<b>606 294 211 108 20</b>		
RG178, 196	RG174, 316, 188	RG316 Double Braid	Hand Formable RG405 (.085)		
Bulkhead Jack	Bulkhead Jack	Bulkhead Jack	Bulkhead Jack		
Ferrule Hex. :128°	Ferrule Hex. :128°	Ferrule Hex. :151°	Solder		

**Important information:** Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on [www.we-online.com](http://www.we-online.com) for specifications.  
Würth Elektronik eSos GmbH & Co. KG, EMC & Inductive Solutions. ©2022

**ALL PRODUCTS  
EX STOCK!**