

TECHNICAL CHARACTERISTICS

MATERIAL
 CONTACT MATERIAL: COPPER ALLOY
 CONTACT TYPE: STAMPED
 CONTACT PLATING: TIN
 QUALITY CLASS: 25 MATING CYCLES
 PITCH: FOR 4.20MM

ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 UP TO 105°C
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 CURRENT RATING: 6 TO 9A
 WORKING VOLTAGE: 600V AC
 INSULATOR RESISTANCE: >1000 MOHM
 DIELECTRIC WITHSTANDING VOLTAGE: 1500V AC/MN
 CONTACT RESISTANCE: 10 MOHM MAX

WIRE DIMENSION
 64910613722 AWG 18-24


PACKAGING
 REEL OF 200 PCS

DIMENSION

ORDER CODE	AWG	A	B	C	D
64910613722	18-24	3.60	4.50	1.90	2.30

RoHS Compliant

G			
F			
E			
D			
C			
B	13-FEB-14	CORRECTIONS	QL
A	CREATION	09-MAR-11	GG
REV	DATE	FILE	BY



APPROVAL: RJ

GENERAL TOLERANCE
 .X = +/- 0.2
 .XX = +/- 0.15

UNIT: MM
 SCALE:
 SHEET: 1/2
 DRAW: MIKE



DESCRIPTION: 4.2MM FEMALE CRIMP TERMINAL 18-24 AWG
 WERI PART NO: 649 106 137 22

SIZE
A4