


# CONNECTORS

## ZIF, LIF & FLEXIBLE CABLES

WR-FPC & WR-FFC



### Special Features

#### Locking types of FPC connectors



#### Features & Benefits

- Maximum cable retention even in small sizes
- Easy insertion system
- Optimized design offering good contact between mating parts
- Nickel under-plating preventing the tin-whisker phenomenon
- UL certified products
- Highly flexible FFCs – fold- and bendable
- Current rating of 0.5 A (0.5 mm pitch) and 1.0 A (1.0 mm pitch)

#### Available Products

- ZIF (Zero-Insertion-Force), LIF (Low-Insertion-Force) and FFC (Flat-Flexible-Cables)
- Straight, right angled & low profile
- Top, bottom, dual & back locking dual contact
- 0.5 and 1.0 mm pitch
- Pin counts: 4 to 30 (1 mm) & 6 to 50 (0.5 mm)
- FFC in 4 standard lengths (50, 100, 152 & 200 mm)
- Folded FFC in 3 variable lengths
- (120 – 200 mm / 165 – 350 mm / 280 – 500 mm)
- Custom length FFC on request (MOQ 5.000)



Visit our online catalogue for detailed product selection:  
[www.we-online.com/FPC-FFC](http://www.we-online.com/FPC-FFC)