

SWITCHES

ROCKER SWITCHES



Features & Benefits

- Trackable safety certification on UL/IEC/CQC 61058-1
- DC rating listed
- 48 h salt spray test
- Glow Wire Test according to IEC 60695-2-11
- UV Test according to IEC 60068-2-5
- IP65 design
- Hot stamping technique on marking
- Customized marking on request (MOQ: 5.000)
- Compliances:



Available Products

- Rectangular types:
 - Panel cut-out: 19.2 x 12.9 mm / 0.187" quick connect terminal (SPST, DPST)
 - Panel cut-out: 30.2 x 22.2 mm / 0.25" quick connect terminal (DPST)
 - Panel cut-out: 27.6 x 13.8 mm / 0.25" quick connect terminal (SPST)
- Round types: Panel cut-out: \varnothing 20.2 mm
 - With 0.187" quick connect terminal (SPST, DPST)
 - With IP65 design (SPST)
 - Illuminated type available in 110 VAC and 220 VAC
- Protection cover for standard round types

ILLUMINATED



\varnothing 20.2 mm



\varnothing 20.2 mm

IP 65



\varnothing 20.2 mm



27.6 x 13.8 mm



19.2 x 12.9 mm

NEW



30.2 x 22.2 mm

Special Features

No worries about aging of plastics!

WE provides UV test reports on Rocker Switches



Need a protection cover?



Visit our online catalogue for detailed product selection:
www.we-online.com/Rocker