

1

2

3

4

5

CHARACTERISTICS:

MATERIAL:

COLOR: BLACK

OPERATING TEMPERATURE: -20°C UP TO 80°C

COMPLIANCE: LEAD FREE AND ROHS


PACKAGING:

10PCS/BAG

WIRE DIMENSION:

AWG: 18

Terminal A



Terminal B

Wire Length 300mm*

Terminal A	649 009 137 22
Terminal B	649 009 137 22

* Note: Wire UL 1007

RoHS Compliant				PROJECTION:	GENERAL TOLERANCE		DESCRIPTION: WR-MPC4 MALE PRE-CRIMPED CONTACT WERI PART NO: 649 949 918 030	SIZE A4
G					.X = +/- 0.2 .XX = +/- 0.15			
F				APPROVAL: RJ	UNIT: MM	DESCRIPTION: WR-MPC4 MALE PRE-CRIMPED CONTACT WERI PART NO: 649 949 918 030	SIZE A4	
E					SCALE:			
D				APPROVAL: RJ DATE: 18-OCT-11 FILE: PDF BY: GG	SHEET: 1/2	DESCRIPTION: WR-MPC4 MALE PRE-CRIMPED CONTACT WERI PART NO: 649 949 918 030	SIZE A4	
C					DRAW: QL			
B								
A	18-OCT-11	PDF	GG					
REV	DATE	FILE	BY					

1

2

3

4

5

A

B

C

D

Note:
 1.Dimension
 Carton Size:40*30*20(CM)
 2.Quantity: 5000 Pcs/Carton



RoHS Compliant

G			
F			
E			
D			
C			
B			
A			
REV	DATE	FILE	BY

PROJECTION:

GENERAL TOLERANCE
 .X = +/- 0.2
 .XX = +/- 0.15

WÜRTH ELEKTRONIK

APPROVAL: RJ

UNIT: MM
 SCALE:
 SHEET: 2/2
 DRAW: QL

DESCRIPTION: WR-MPC4 MALE PRE-CRIMPED CONTACT
 WERI PART NO: 649 949 918 030

SIZE
A4