

TECHNICAL CHARACTERISTICS

MATERIAL
INSULATOR: PBTG7
FLAMMABILITY RATING: UL94V0
COLOR: BLACK
METAL: PHOSPHOR BRONZE
PLATING: TIN



ENVIRONMENTAL
OPERATING TEMPERATURE: -40°C UP TO +125°C
COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
CURRENT RATING: 3A Max
WITHSTANDING VOLTAGE: 500VAC
CONTACT RESISTANCE: 20 mΩ MAX

MECHANICAL
SOLID WIRE: 28-26 AWG / 0,08-0,128 mm²

PACKAGING
TUBES (220 contacts per row)

A = (nb. pin-1) x pitch
B = (nb. pin x pitch)

RoHS Compliant				<div>PROJECTION:</div> <div></div>	<div>GENERAL TOLERANCE</div> <div>±0,1</div>	<div></div> <div>WÜRTH ELEKTRONIK</div>	
G							
F							
E							
D							
C				<div>APPROVAL: QL</div>	UNIT: MM	<div>DESCRIPTION: WIRE TO BOARD CONNECTION - 2.54 MM - IDC - IDC CONNECTOR - WR-WTB</div>	SIZE A4
B					SCALE:		
A	19-SEP-14	PDF	AK		SHEET: 1/2		
REV	DATE	FILE	BY		DRAW: AK		

