




PCB LAYOUT - COMPONENT VIEW



TECHNICAL CHARACTERISTICS

MATERIAL
 INSULATOR: PA 6T
 FLAMMABILITY RATING: UL94-V0
 COLOR: BLACK
 CONTACT MATERIAL: COPPER ALLOY
 CONTACT TYPE: STAMPED
 CONTACT PLATING: GOLD
 QUALITY CLASS: 3 AS PER CECC 75 301-802
 PITCH: 2.54 MM

ENVIRONMENTAL
 OPERATING TEMPERATURE: -40 UP TO 125°C
 COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL
 CURRENT RATING: 3 A
 WORKING VOLTAGE: 250 VAC
 INSULATOR RESISTANCE: >1000 MOHM
 DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC/MN
 CONTACT RESISTANCE: 20 MOHM MAX

STANDARD
 CERTIFIED: E323964

SOLDERING
 JEDEC LEAD FREE REFLOW SOLDERING

PACKAGING
 TUBE

DIMENSION
 A = 2.54 x (NB. PIN /2 - 1)
 B = 2.54 x (NB. PIN /2)

RoHS Compliant			
G			
F			
E	29-MAR-17	DRAWING	AK
D	23-AUG-10	PACKAGING	JC
C	25-NOV-09	STANDARD	JP
B	21-NOV-08	COPLANARITY	JP
A	06-NOV-08	PDF	JP
REV	DATE	FILE	BY






PROJECTION:	
APPROVAL: GMo	

GENERAL TOLERANCE	
.X = +/- 0.2	
.XX = +/- 0.15	
UNIT: MM	
SCALE:	
SHEET: 1/3	
DRAW: MIKE WU	


	DESCRIPTION: 2.54MM SMT DUAL SOCKET BOTTOM ENTRY
	WERI PART NO: 610 0xx 243 021

SIZE	A4

A
B
C
D



INNER CARTON



CARTON

Note:
 1,Dimension
 Tube Size: L=635mm
 Inner Carton Size:680(L)X330(W)X160(H) (mm)
 Carton Size:655(L)X152(W)X140(H) (mm)

Pin	Pcs/Tube	Tube/Inner Carton	Pcs/Inner Carton	Pcs/Carton
4	121	160	19360	77440
6	80	160	12800	51200
8	60	160	9600	38400
10	48	160	7680	30720
12	40	160	6400	25600
14	34	160	5440	21760
16	30	160	4800	19200
18	26	160	4160	16640
20	24	160	3840	15360
22	22	160	3520	14080
24	20	160	3200	12800
26	18	160	2880	11520
28	17	160	2720	10880
30	16	160	2560	10240
32	15	160	2400	9600
34	14	160	2240	8960
36	13	160	2080	8320
38	12	160	1920	7680
40	12	160	1920	7680

RoHS Compliant

G			
F			
E			
D			
C			
B			
A			
REV	DATE	FILE	BY

PROJECTION:

GENERAL TOLERANCE
 .X = +/- 0.2
 .XX = +/- 0.15



APPROVAL: GMo

UNIT: MM
 SCALE:
 SHEET: 2/3
 DRAW: PEARL

DESCRIPTION: 2.54MM SMT DUAL SOCKET BOTTOM ENTRY
 WERI PART NO: 610 0xx 243 021

SIZE
A4