1	2		3		4	5		Γ
I	B ±0,3	4,05	Ø 1,3		TECHNICAL CHARACTERIS MATERIAL INSULATOR: PA6/66 FLAMMABILITY RATING: UL COLOR: GREEN METAL HOUSING: COPPER TERMINAL SCREW: STEEL WIRE GUARD: COPPER ALI ENVIRONMENTAL OPERATING TEMPERATUR COMPLIANCE: LEAD FREE ELECTRICAL CURRENT RATING: WORKING VOLTAGE: WITHSTANDING VOLTAGE: CONTACT RESISTANCE: STANDARD CERTIFIED: E150931 CERTIFIED: 40021365 MECHANICAL SOLID WIRE: 30-14 STRANDED WIRE: 30-14 TORQUE: WIRE STRIPE LENGTH: 6 m SCREW: M3	STICS 94V0 R ALLOY / Ni+Sn / Zn LOY / Ni+Sn E: -30°C UP TO +120°C AND ROHS UL VDE 14 A 14 A 300 VAC 250 VAC 1,6 KV 2 KV 20 mΩ MAX CAT. N°: CIA (4) TYPE: CIA AWG / 0,05-2,08 mm ² AWG / 0,05-2,08 mm ² AWG / 0,05 Nm		B
RoHS Compliant Image: Compliant G Image: Compliant F Image: Compliant D Image: Compliant D Image: Compliant B Image: Compliant			A = (nb. pin- B = (nb. pin B = (nb. pin ±0,1	x pitch)	RIE 2415 - 5.08 MM - HORIZON	NTAL CABLE ENTRY WITH	SIZE	
A 18-AUG-14 PDF REV DATE FILE			SHEET: 1/2 DRAW: AK	WERI PART NO: 69	241 510 0xx		A4	

1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	RoHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE			1
F								
E								
D				1		WÜRTH ELEKTRONIK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	Ъ
В]	SCALE:			٢
A	10-SEP-14	PDF	QL]	SHEET: 2/2	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			