


# ASSEMBLY TECHNOLOGY – PLASTIC



more details online

|                                                                                                                                            |                                                                                                                                              |                                                                                                                                              |                                                                                                                                                                |                                                                                                                                    |                                                                                                                                            |                                                                                                                                            |
|--------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------|
| <b>WA-CHFCHAD</b><br><b>524 25x 000</b><br>Flat Cable Clamp with Arrow Head – Self-Adhesive<br>Flat Cable Size: 32 mm                      | <b>WA-CHFCHAD</b><br><b>524 21x 000</b><br>Miniature Flat Cable Clamp – Self-Adhesive<br>Width: 15 – 25.4 mm                                 | <b>WA-CHAD</b><br><b>523 2xx 000</b><br>Adhesive Cable Mount Clip – Opening Sideways<br>Type 1 & Type 2                                      | <b>WA-CHAD</b><br><b>521 2x0 000</b><br>Cable Holder – Self-Adhesive<br>Height: 7.4 – 18.1 mm                                                                  | <b>WA-CHAD</b><br><b>522 2x0 000</b><br>Miniature Cable Holder – Self-Adhesive<br>Height: 6.6 – 14.3 mm                            | <b>WA-CTIB</b><br><b>530 9xx x00</b><br>Two-Way Base – Self-Adhesive<br>13 x 4 mm, 19.1 x 4.8 mm<br>20 x 5 mm, 25.4 x 7.9 mm               | <b>WA-CHTW</b><br><b>520 2xx 000</b><br>Twister for Cables – Self-Adhesive Base<br>Inner-Ø closed: Ø 7.2 – Ø 13.8 mm                       |
| <b>WA-FCHSN</b><br><b>524 4x0 000</b><br>Flat Cable Clamp – Arrow Head<br>Flat Cable Size: 32 mm                                           | <b>WA-CHCL</b><br><b>500 91x x00</b><br>Cable Clip<br>Inner-Ø closed: Ø 3 – Ø 15.5 mm                                                        | <b>WA-CHSN</b><br><b>521 41x 000</b><br>Snap-In Cable Holder – flexible Clamp Straps<br>Snap locking Ø 4.8 – Ø 5 mm<br>Height: 12 – 34 mm    | <b>WA-CHSN</b><br><b>521 4xx 000</b><br>Snap-In Cable Holder – Locking Top<br>Snap locking Ø 4.8 – Ø 5 mm<br>Height: 9 – 27.2 mm                               | <b>WA-CHSN</b><br><b>521 44x 000</b><br>Snap-In Cable Holder – Locking Top<br>Snap locking Ø 3.5 mm<br>Height: 9 – 14.2 mm         | <b>WA-CHSN</b><br><b>522 4x0 000</b><br>Miniature Cable Holder – Snap-In Device<br>Snap locking Ø 3.0 & Ø 3.5 mm<br>Height: 7.3 mm         | <b>WA-CHTW</b><br><b>520 40x 000</b><br>Standoff Twister for Cables<br>Snap locking Ø 4.8 – Ø 5 mm<br>Inner-Ø closed: Ø 6.1 – Ø 13.8 mm    |
| <b>WA-SNAD</b><br><b>709 26x 000</b><br>Snap-In Stop Spacer – Self Adhesive<br>Snap Locking Ø 4 mm<br>Distance: 6.4 & 12.9 mm              | <b>WA-SNFR</b><br><b>709 44x x00</b><br>Snap-In Spacer – Reverse Mount<br>Snap Locking Ø 3 & Ø 4 mm<br>Distance: 2.5 – 16 mm                 | <b>WA-SNFR</b><br><b>709 44x x00</b><br>Snap-In Spacer – Reverse Mount<br>Snap Locking Ø 4 & Ø 5.5 mm<br>Distance: 5 – 14 mm                 | <b>WA-SNTE / WA-SNSH / WA-SCRW / WA-EXRV</b><br><b>709 940 x00 / 70995ST33 / 9779 xx0 3111 / 709974200</b><br>Parts for Assembly<br>Screws, Nuts & Snap Rivets | <b>WA-SNRM</b><br><b>709 85x 000</b><br>Snap Rivet Mount Spacer<br>Snap locking Ø 4 mm<br>Distance: 9.5 – 25.4 mm                  | <b>WA-SNTE</b><br><b>709 905 6x1</b><br>Snap-In Stop Spacer – M3<br>Snap locking Ø 3.18 mm<br>Distance: 3.2 – 14.3 mm                      | <b>WA-SNTE</b><br><b>709 905 6x0</b><br>Snap-In Stop Spacer – M4<br>Snap locking Ø 4 mm<br>Distance: 6.4 – 22.2 mm                         |
| <b>WA-SNSR</b><br><b>702 91x 000</b><br>Self Retaining Spacer<br>Snap Locking Ø 3 mm<br>Distance: 2 – 8 mm                                 | <b>WA-SNSR</b><br><b>702 92x 000</b><br>Self Retaining Spacer<br>Snap Locking Ø 4 mm<br>Distance: 2.5 – 6 mm                                 | <b>WA-SNSR</b><br><b>702 93x x00</b><br>Self Retaining Spacer<br>Snap Locking Ø 4.8 mm<br>Distance: 4 – 22.2 mm                              | <b>WA-SNSR</b><br><b>702 94x x00</b><br>Self Retaining Spacer<br>Snap Locking Ø 5.9 mm<br>Distance: 6.4 – 17 mm                                                | <b>WA-SNSH</b><br><b>709 95x 000</b><br>Snap-In Spacer – Screw Mount<br>Snap locking Ø 4 mm<br>Distance: 6.4 – 19.2 mm             | <b>WA-SNSN</b><br><b>709 40x x00</b><br>Snap-In Stop Spacer<br>Snap locking Ø 4.8 mm<br>Distance: 4.8 – 25.4 mm                            | <b>WA-SNSN</b><br><b>709 62x x00</b><br>Snap-In Spacer Snap – Locking on both Ends<br>Snap locking Ø 4 mm<br>Distance: 3 – 30 mm           |
| <b>WA-SNSN</b><br><b>709 65x x00</b><br>Miniature Snap-In Spacer – Snap Locking on both Ends<br>Snap locking Ø 2 mm<br>Distance: 3 – 14 mm | <b>WA-SNSN</b><br><b>709 670 xx0</b><br>Miniature Snap-In Spacer – Snap Locking on both Ends<br>Snap locking Ø 2.5 mm<br>Distance: 3 – 20 mm | <b>WA-SNSN</b><br><b>709 65x xx0</b><br>Miniature Snap-In Spacer – Snap Locking on both Ends<br>Snap locking Ø 3.5 mm<br>Distance: 3 – 20 mm | <b>WA-SNSN</b><br><b>701 51x x00</b><br>Snap-In Keyslot – Snap Lockin on both Ends<br>Snap locking Ø 3.2 mm<br>Inner-Ø closed: Ø 6.1 – Ø 13.8 mm               | <b>WA-SNSN</b><br><b>701 52x x00</b><br>Snap-In Keyslot – Snap Lockin on both Ends<br>Snap locking Ø 4 mm<br>Distance: 3.2 – 22 mm | <b>WA-SNSN</b><br><b>709 61x x00</b><br>Snap-In Stop Spacer – Snap Locking on both Ends<br>Snap locking Ø 4 mm<br>Distance: 4.74 – 28.6 mm | <b>WA-SNSN</b><br><b>709 61x x00</b><br>Snap-In Stop Spacer – Snap Locking on both End<br>Snap locking Ø 4.8 mm<br>Distance: 4.6 – 22.2 mm |

PASSIVE COMPONENTS | **ELECTROMECHANICAL COMPONENTS** | POWER MODULES | OPTOELECTRONICS | THERMAL MANAGEMENT | CUSTOM MAGNETICS | AUTOMOTIVE | WIRELESS CONNECTIVITY & SENSORS

**Important information:** Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on [www.we-online.com](http://www.we-online.com) for specifications. Würth Elektronik eiSos GmbH & Co. KG, EMC & Inductive Solutions. ©2024

**ALL PRODUCTS  
EX STOCK!**