



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-8 @20°C	0.222 ohms ±10%
D.C. RESISTANCE	2-7 @20°C	0.100 ohms ±20%
D.C. RESISTANCE	4-5 @20°C	0.095 ohms ±20%
INDUCTANCE	1-8 10kHz, 100mVAC, Ls	56uH ±10%
SATURATION CURRENT	1-8 20% rolloff from initial	1.25A
LEAKAGE INDUCTANCE	1-8 tie(2+7, 4+5), 100kHz, 100mVAC, Ls	3.5uH typ., 7uH max.
DIELECTRIC	1-4 tie(7+8), 1250VAC, 1 second	1000VAC, 1 minute
DIELECTRIC	1-2 625VAC, 1 second	500VAC, 1 minute
TURNS RATIO	(1-8):(2-7)	2.88:1, ±2%
TURNS RATIO	(1-8):(4-5)	2.88:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Safety standard undefined.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0193 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750313266
6A	2/19	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750313266	SPECIFICATION SHEET 1 OF 1