


CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect





**ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	5-19 tie(5+6+7, 17+18+19), @20°C	0.005 ohms max.
INDUCTANCE	5-19 tie(5+6+7, 17+18+19), 10kHz, 100mV, Ls	34.50µH ±10%
SATURATION CURRENT	5-19 tie(5+6+7, 17+18+19), 20% rolloff from initial	37A
DISTRIBUTED CAPACITANCE	5-19 tie(5+6+7, 17+18+19), 100mVAC, Cs	5.5pF typ.



Update at release to show all 22 pins. Update hole size to 1.5mm at release. CHC 7/19/18



**GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.  
Rated rms current: 20 Amps

*Preliminary*

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1°    Decimals: ±.005 [.13] Fractions: ±1/64    Footprint: ±.001 [.03]	DRAWING TITLE	PART NO.
DATE	Method: Tray		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	<b>INDUCTOR</b>	<b>750317850</b>
ENG	CHC				
REV.	01				
DATE	1/10/2020	www.we-online.com/midcom			SPECIFICATION SHEET 1 OF 1