




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	4-5 @20°C	0.96 ohms max.
D.C. RESISTANCE	1-2 @20°C	0.22 ohms max.
D.C. RESISTANCE	6-8 @20°C	0.08 ohms max.
D.C. RESISTANCE	7-9 @20°C	0.09 ohms max.
INDUCTANCE	4-5 10kHz, 100mVAC, Ls	700uH ±10%
LEAKAGE INDUCTANCE	4-5 tie(1+2+6+7+8+9), 100kHz, 100mVAC, Ls	5.5uH typ., 7.7uH max.
DIELECTRIC	1-9 tie(2+3, 6+7), 3750VAC, 1 second	3000VAC, 1 minute
TURNS RATIO	(4-5):(1-2)	5.25:1, ±2%
TURNS RATIO	(4-5):(6-8)	6.46:1, ±2%
TURNS RATIO	(4-5):(7-9)	6.46:1, ±2%

PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID



Wire insulation & RoHS status not affected by wire color.
 Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0988 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$	Decimals: $\pm .005$ [.13] Footprint: $\pm .001$ [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750341114
6A	4/15	SEE REVISION SHEET FOR REVISION LEVEL	REVISION LEVEL	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		eiSos p/n: 750341114	SPECIFICATION SHEET 1 OF 1