


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	6-4 @20°C	2.76 ohms max.
D.C. RESISTANCE	S-F @20°C	0.030 ohms max.
D.C. RESISTANCE	7-5 @20°C	0.750 ohms max.
INDUCTANCE	6-4 50kHz, 100mVAC, Ls	1.60mH ±10%
LEAKAGE INDUCTANCE	6-4 tie(5+7, S+F), 100kHz, 100mVAC, Ls	50uH max.
DIELECTRIC	6-S 1875VAC, 1 second	1500VAC, 1 minute
DIELECTRIC	6-Core 1875VAC, 1 second	1500VAC, 1 minute
DIELECTRIC	S-Core 1875VAC, 1 second	1500VAC, 1 minute
TURNS RATIO	(6-4):(7-5)	5:1, ±2%
TURNS RATIO	(6-4):(S-F)	15:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0117 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.001 [.03]	DRAWING TITLE TRANSFORMER	PART NO. 750341723
6B	7/20			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750341723	
6A	3/14	SEE REVISION SHEET FOR REVISION LEVEL				SPECIFICATION SHEET 1 OF 1