



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

D.C. RESISTANCE (@20°C):	3-1 , 1.52 Ohms $\pm 10\%$. 11-8 , 0.20 Ohms $\pm 10\%$. 6-5 , 0.45 Ohms $\pm 10\%$.
DIELECTRIC RATING:	1500VAC, 1 minute tested by applying 1875VAC for 1 second between pins 1-11 (tie 3+5).
INDUCTANCE:	1.52 mH $\pm 10\%$, 10KHz, 100mVAC, 0mADC, 3-1, Ls.
LEAKAGE INDUCTANCE:	13.8 μ H Typ. 18.0 μ H Max., 100KHz, 100mVAC, 3-1(5+6, 8+11), Ls.
TURNS RATIO:	(3-2):(2-1) , (1):(1.00) , $\pm 2\%$. (3-1):(11-8) , (4.00):(1.00) , $\pm 2\%$. (3-1):(6-5) , (5.525):(1.00) , $\pm 2\%$.

Designed to meet Functional Insulation Only

OPERATING TEMPERATURE RANGE: -40°C to 125°C including temp. rise.

WE-Midcom, Inc. Watertown, SD USA Toll Free: 800-643-2661 Fax: 605-886-4486	Unless otherwise specified, tolerances are as follows: Angles: $\pm 1^\circ$ Fractions: $\pm 1/64$ Decimals: $\pm .005$ (.127mm)		WE-Midcom, Inc.	
	Drawing Title Transformer		Drawing Number 750312496	Rev. 00
This drawing is dual dimensioned. Dimensions in brackets are in millimeters	Revisions: See Sheet 1 Engineer:KSM		Scale ----	Sheet 2 of 5 01/20/2012