


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes


more than you expect





TERM. NO.'s FOR REF. ONLY  
.130/.150  
[3.30/3.81]



Ø.024(8)  
[.60]  
PART MUST INSERT FULLY TO  
SURFACE A IN TRUE POSITION GRID



ALTERNATE MARKING DETAIL



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-8 @20°C	2.463 ohms max.
D.C. RESISTANCE	3-6 @20°C	0.295 ohms max.
D.C. RESISTANCE	4-5 @20°C	0.304 ohms max.
INDUCTANCE	1-8 100kHz, 1.0VAC, Ls	3.80mH ±5.3%
DIELECTRIC	tie(3+4), 500VAC, 1 second	-
TURNS RATIO	(1-8):(3-6)	27.5:1, ±2%
TURNS RATIO	(1-8):(4-5)	27.5:1, ±2%

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications Method: Tray PKG-0887 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [ .13 ] Footprint: ±.001 [ .03 ]	DRAWING TITLE <b>INDUCTOR</b>	PART NO. <b>750341978</b>
6B	12/13			This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750341978	SPECIFICATION SHEET 1 OF 1
6A	10/13	SEE REVISION SHEET FOR REVISION LEVEL				