



CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-7 tie(1+2+3,7+8+9), @20°C	0.025 ohms max.
INDUCTANCE	1-7 tie(1+2+3,7+8+9),50kHz, 100mV, Ls	50.0µH ±10%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Customer to tie terminals 1&2&3 and 7&8&9 internally on PCB.

Application of the transformer allows for the leadwire between terminal #1&2&3 and 7&8&9 to solder bridge.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM		Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13] Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]	DRAWING TITLE INDUCTOR	PART NO.
DATE		Method: Tray		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		750343007
ENG	YGD	PKG-0825				
REV.	01					
DATE	1/20/2016	www.we-online.com/midcom				SPECIFICATION SHEET 1 OF 1