


CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96%, Ag4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-6 tie(1+2, 5+6), @20°C	0.035 ohms max,
INDUCTANCE	1-6 tie(1+2, 5+6), 10kHz, 100mVAC, Ls	25uH ±10%
SATURATION CURRENT	1-6 tie(1+2, 5+6), 20% rolloff from initial	12A

GENERAL SPECIFICATIONS:  
OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.  
CURRENT RATING: 3A

Wire insulation & RoHS status not affected by wire color.  
Wire insulation color may vary depending on availability.

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64	Decimals: ±.005 Footprint: ±.001	DRAWING TITLE	PART NO.
		Method: Tray PKG-0239 www.we-online.com/midcom				<b>INDUCTOR</b>	<b>750344650</b>
6A	8/22	SEE REVISION SHEET FOR REVISION LEVEL		This drawing is dual dimensioned. Dimensions in brackets are in millimeters.		eiSos p/n: 750344650	SPECIFICATION SHEET 1 OF 1

