





\* DIMENSION MAY BE EXCEEDED WITH SOLDER ONLY







RECOMMENDED P.C. PATTERN, COMPONENT SIDE



OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Designed to comply with the following requirements as defined by IEC60950-1,

EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:

**GENERAL SPECIFICATIONS:** 

- Reinforced insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak, Overvoltage Category II.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM Packaging Specifications
DATE Method: Tray
ENG NWA
REV. 00
DATE 2015-09-17 www.we-online.com/midcom

Tolerances unless otherwise specified:

Angles: ±1° Decimals: ±.005 [.13]

Fractions: ±1/64 Footprint: ±.001 [.03]

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

TRANSFORMER

DRAWING TITLE

PART NO.

750343026

SPECIFICATION SHEET 1 OF 1