

CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes


more than you expect





**ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:**

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-4 @20°C	8.310 ohms max.
D.C. RESISTANCE	S-F @20°C	0.008 ohms max.
INDUCTANCE	3-4 50kHz, 100mV, Ls	16.0mH min.
DIELECTRIC	3-S 3750VAC, 1 second	3000VAC, 1 minute
DIELECTRIC	S-core 3750VAC, 1 second	3000VAC, 1 minute
URNS RATIO	(3-4):(S-F)	170:1, ±2%

PART MUST INSERT FULLY TO SURFACE A IN RECOMMENDED GRID



TERM. NO.'s FOR REF. ONLY  
LOT CODE & DATE CODE



RECOMMENDED P.C. PATTERN, COMPONENT SIDE

**GENERAL SPECIFICATIONS:**

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.  
 Designed to comply with the following requirements as defined by IEC60950-1, EN60950-1, UL60950-1/CSA60950-1 and AS/NZS60950.1:  
 - Reinforced insulation for a primary circuit at a working voltage of 265Vrms, 400Vpeak, Overvoltage Category II.  
 Current Rating: 4A(Pin S-F)

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM		Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified: Angles: ±1°    Decimals: ±.005 [.13] Fractions: ±1/64    Footprint: ±.001 [.03]	DRAWING TITLE	PART NO.
DATE		Method: Tray				
ENG	NWA	PKG-0000				
REV.	01					
DATE	2016-01-26	www.we-online.com/midcom				SPECIFICATION SHEET 1 OF 1