




CUSTOMER TERMINAL	RoHS	LEAD(Pb)--FREE
Sn 96%, Ag 4%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25° C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	3-1 @20°C	0.956 ohms max.
D.C. RESISTANCE	4-6 @20°C	0.655 ohms max.
INDUCTANCE	3-1 500kHz, 100mV, Ls	400.00µH ±20%
LEAKAGE INDUCTANCE	4-6 tie(3+1),500kHz, 100mV, Ls	15.20µH ±10%
DIELECTRIC	1-6 1000VAC, 1 second	
URNS RATIO	(3-2):(2-1)	1:1, ±2%
URNS RATIO	(4-6):(3-2)	1.45:1, ±2%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

Wire insulation & RoHS status not affected by wire color. Wire insulation color may vary depending on availability.

DFM	Packaging Specifications	 CONVENTION PLACEMENT	Tolerances unless otherwise specified:	DRAWING TITLE	PART NO.
DATE	Method: Tape & Reel		Angles: ±1° Decimals: ±.005 [.13]		
ENG	PKG-0519	Fractions: ±1/64 Footprint: ±.005 [.13]	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	SPECIFICATION SHEET 1 OF 1	
REV.	02				
DATE	8/20/2019	www.we-online.com/midcom			