














Board Stack Report

Stack Up		Layer Stack			
Layer	Board Layer Stack	Name	Material	Thickness	Constant
1		Top Paste			
2		Top Overlay			
3		Top Solder	Solder Resist	0,030mm	3,5
4		Top Side	Copper	0,040mm	
5		Dielectric 1	FR-4 1080 2116 TG135	0,170mm	4
6		Ref Ground TS	Copper	0,033mm	
7		Dielectric 3	FR-4	0,250mm	4,1
8		Ref Ground BS	Copper	0,033mm	
9		Dielectric 4	FR-4 1080 2116 TG135	0,170mm	4
10		Bottom Side	Copper	0,040mm	
11		Bottom Solder	Solder Resist	0,030mm	3,5
12		Bottom Overlay			
13		Bottom Paste			

Height : 0,796mm