



中国认可  
国际互认  
检测  
TESTING  
CNAS L0167

# TEST REPORT

No. : GZMR230701896401-1

Date : Aug 15, 2023

Page: 1 of 6



CUSTOMER NAME: WURTH ELECTRONICS(SHENZHEN) CO.,LTD  
ADDRESS: 1-3ND FLOOR,BIO-TECH MAIN BUILDING,PUZAI  
RD#22, LONGGANG DIST., SHENZHEN GUANGDONG

Sample Name : ROCKER SWITCH  
Model No. : RSTV 471 023 xxx xxx  
Material No. : 471023262153  
Manufacturer : WÜRTH ELEKTRONIK EISOS GMBH&CO.KG  
Buyer : WÜRTH ELEKTRONIK EISOS GMBH&CO.KG

Above information and sample(s) was/were submitted and confirmed by the client. SGS, however, assumes no responsibility to verify the accuracy, adequacy and completeness of the sample information provided by client.

\*\*\*\*\*

SGS Ref. No. : CP23-024724  
Date of Receipt : Jul 07, 2023  
Testing Start Date : Jul 07, 2023  
Testing End Date : Aug 03, 2023  
Test result(s) : For further details, please refer to the following page(s)  
(Unless otherwise stated the results shown in this test report refer only to the sample(s) tested)

Signed for  
SGS-CSTC Standards Technical  
Services Co., Ltd. Guangzhou Branch

Kelly Lee  
Authorized signatory



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <http://www.sgs.com/en/Terms-and-Conditions.aspx> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <http://www.sgs.com/en/Terms-and-Conditions/Terms-e-Documents.aspx>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.  
Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: [CN.Doccheck@sgs.com](mailto:CN.Doccheck@sgs.com)  
□ No.198, Kiechu Road, Science City Economic & Technology Development Area, Guangzhou, Guangdong, China □ Room 101, Building 3, No.1501, Kaichang Avenue, Huangpu District, Guangzhou, China (86-20) 8215555 [www.sgsgroup.com.cn](http://www.sgsgroup.com.cn)  
中国·广东·广州高新技术产业开发区科学城科珠路198号 中国·广东·广州市黄埔区开创大道1501号3栋101房 (86-20) 8215555 [sgs.china@sgs.com](mailto:sgs.china@sgs.com)

# TEST REPORT

No. : GZMR230701896401-1

Date : Aug 15, 2023

Page: 2 of 6

Summary of Results:

No.	Test Item	Test Method	Result	Conclusion
1	Glowing-Wire Test (GWEPT)	IEC 60695-2-11:2021	GWEPT:750	Pass

Note: Pass : Meet the requirements;  
 Fail : Does not meet the requirements;  
 / : Not Apply to the judgment.



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <http://www.sgs.com/en/Terms-and-Conditions.aspx> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <http://www.sgs.com/en/Terms-and-Conditions/Terms-e-Documents.aspx>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.

Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: [CN.Doccheck@sgs.com](mailto:CN.Doccheck@sgs.com)

No.198, Kechu Road, Science City, Economic & Technology Development Area, Guangzhou, Guangdong, China  
  Room 101, Building 3, No.1501, Kaichang Avenue, Huangpu District, Guangzhou, China  
 t(86-20) 8215555  
 www.sgsgroup.com.cn  
 中国·广东·广州高新技术产业开发区科学城科珠路198号  
 中国·广东·广州市黄埔区开创大道1501号3栋101房  
 t(86-20) 8215555  
 sgs.china@sgs.com

# TEST REPORT

No. : GZMR230701896401-1

Date : Aug 15, 2023

Page: 3 of 6

Test Item: Glowing-Wire Test (GWEPT)

Sample Description: Finished product

Test Method: IEC 60695-2-11:2021

Test Condition:

Pre-treatment: (23±2) °C, (50±5) %RH, 24h

The time of application of the glow-wire  $t_{APP}$ : 30 s

Test Result:

Specimen No.	Test Temp. (°C)	$t_i$ (s)	$t_E$ (s)	$t_R$ (s)	Whether the specimen is ignition	Whether the specified layer is ignition
1	750	1.0	10.0	0	Yes	No
2	750	0.5	6.5	0	Yes	No
3	750	0.5	8.0	0	Yes	No
4	750	0.5	7.5	0	Yes	No
5	750	0.5	30.0	0	Yes	No
6	750	0.5	30.5	0.5	Yes	No
7	750	1.0	16.5	0	Yes	No
8	750	0.5	7.5	0	Yes	No
9	750	0.5	7.5	0	Yes	No
10	750	0.5	8.5	0	Yes	No
11	750	0.5	9.5	0	Yes	No
12	750	0.5	8.0	0	Yes	No
13	750	0.5	7.0	0	Yes	No
14	750	0.5	30.5	0	Yes	No
15	750	0.5	7.0	0	Yes	No
16	750	0.5	12.0	0	Yes	No
17	750	0.5	9.5	0	Yes	No
18	750	0.5	31.0	1.0	Yes	No
19	750	0.5	31.0	1.0	Yes	No
20	750	0.5	30.5	0.5	Yes	No



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <http://www.sgs.com/en/Terms-and-Conditions.aspx> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <http://www.sgs.com/en/Terms-and-Conditions/Terms-e-Documents.aspx>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.

Attention: To check the authenticity of testing / inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: CN.Doccheck@sgs.com

No.198, Kexu Road, Science City, Economic & Technology Development Area, Guangzhou, Guangdong, China  
  Room 101, Building 3, No.1501, Kaichuang Avenue, Huangpu District, Guangzhou, China  
 (86-20) 8215555  
 www.sgs.com.cn  
 Guangzhou Branch Testing Services & Reliability Laboratory  
 中国·广东·广州高新技术产业开发区科学城科珠路198号  
 中国·广东·广州市黄埔区开创大道1501号3栋101房  
 (86-20) 8215555  
 sgs.china@sgs.com

# TEST REPORT

No. : GZMR230701896401-1

Date : Aug 15, 2023

Page: 4 of 6

21	750	0.5	12.5	0	Yes	No
22	750	0.5	13.5	0	Yes	No
23	750	0.5	18.0	0	Yes	No
24	750	0.5	11.0	0	Yes	No
25	750	0.5	21.0	0	Yes	No
26	750	0.5	9.0	0	Yes	No
27	750	0.5	10.5	0	Yes	No
28	750	0.5	30.5	0.5	Yes	No
29	750	0.5	7.5	0	Yes	No
30	750	0.5	10.5	0	Yes	No
GWEPT:750						

Client's requirement: GWEPT:750

Conclusion: Pass

Note:

1.  $t_I$  - The time from the start of test, at which the longest persisting flame event starts;
2.  $t_E$  - The time from the start of the test, at which the longest persisting flame event ends;
3.  $t_R$  - Time elapsed after the removal of the glow-wire tip from the test specimen to the end of the longest persisting flame event;
4. Test criteria:
  - a) there is no ignition, or
  - b) all the following situations apply when ignition has occurred:
    - i. flames or glowing combustion of the test specimen extinguish within 30s after removal of the glow-wire, i.e.  $t_R \leq 30s$ ; and
    - ii. the specified layer placed underneath the test specimen does not ignite.
5. The specified layer was the wrapping tissue.



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <http://www.sgs.com/en/Terms-and-Conditions.aspx> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <http://www.sgs.com/en/Terms-and-Conditions/Terms-e-Document.aspx>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.

Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: CN.Doccheck@sgs.com

No.198, Kechu Road, Science City, Economic & Technology Development Area, Guangzhou, Guangdong, China  
  Room 101, Building 3, No.1501, Kaichuang Avenue, Huangpu District, Guangzhou, China  
 (86-20) 8215555  
 www.sgsgroup.com.cn  
 中国·广东·广州高新技术产业开发区科学城科珠路198号  
 中国·广东·广州市黄埔区开创大道1501号3栋101房  
 (86-20) 8215555  
 sgs.china@sgs.com


## TEST REPORT

No. : GZMR230701896401-1

Date : Aug 15, 2023

Page: 5 of 6

Test Photo:



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <http://www.sgs.com/en/Terms-and-Conditions.aspx> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <http://www.sgs.com/en/Terms-and-Conditions/Terms-e-Documents.aspx>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.

**Attention: To check the authenticity of testing / inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: CN.Doccheck@sgs.com**

No.198, Kechu Road, Science City, Economic & Technology Development Area, Guangzhou, Guangdong, China   
  Room 101, Building 3, No.1501, Kaichuang Avenue, Huangpu District, Guangzhou, China   
 (86-20) 8215555    www.sgsgroup.com.cn  
 中国·广东·广州高新技术产业开发区科学城科珠路198号    中国·广东·广州市黄埔区开创大道1501号3栋101房    (86-20) 8215555    sgs.china@sgs.com

# TEST REPORT

No. : GZMR230701896401-1

Date : Aug 15, 2023

Page: 6 of 6

Equipment Information:

Equipment	Model	Equipment No.	Calibration date	Next Calibration date
Glow Wire Tester	ZLT-GTR	GZMR-PL-E246	2023-01-13	2024-01-12

Appendix information:

1. This test report supersedes test report No. GZMR230701896401, the original test report is void.
2. This report deletes product specification.

\*\*\*\*\* End of report\*\*\*\*\*



Unless otherwise agreed in writing, this document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at <http://www.sgs.com/en/Terms-and-Conditions.aspx> and, for electronic format documents, subject to Terms and Conditions for Electronic Documents at <http://www.sgs.com/en/Terms-and-Conditions/Terms-e-Documents.aspx>. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 30 days only.

**Attention: To check the authenticity of testing /inspection report & certificate, please contact us at telephone: (86-755) 8307 1443, or email: CN.Doccheck@sgs.com**

No.198, Kechu Road, Science City, Economic & Technology Development Area, Guangzhou, Guangdong, China  
  Room 101, Building 3, No.1501, Kaihuang Avenue, Huangpu District, Guangzhou, China  
 t(86-20) 8215555   www.sgsgroup.com.cn  
 Guangzhou Branch Testing, Reliability & Reliability Laboratory  
 中国·广东·广州高新技术产业开发区科学城科珠路198号  
 中国·广东·广州市黄埔区开创大道1501号3栋101房  
 t(86-20) 8215555   sgs.china@sgs.com