




Special Features



Screwless connections for fast mounting




Robust screw connections for high mechanical load



Full automation for fast and very precise positioning on the PCB



Optimal solder pad geometry and specially developed plating for constant and reliable soldering results



High holding forces and torques for safe and strong mechanical connection



Tab on the polyimide foil for instant removal

Features & Benefits

- Fast and precise process
- Instant removable polyimide foil
- Strong holding forces and torques
- Highest process reliability
- Customized length upon request (with MOQ)

	Length	Thread size	Hole ϕ
Internal thread	1 to 16 mm	M1.6 to M5	
Through hole	1 to 16 mm		2.25 to 4.50 mm
External thread	5 to 15 mm	M3	
Reverse type	1 to 10 mm (using standard PCB 1.6 mm)	M3	3.20 mm
Right angled with pin or right angled block thread		M2 to M3	3.30 mm
Accessories:	<ul style="list-style-type: none"> ■ Mounting button for M3 and snap rivet for fast and tool free mounting ■ Distance cap & fitting plastic screw (M3) (for spacers with 6 mm outer diameter, starting at 2.5 mm height) 		



Visit our online catalogue for detailed product selection:
www.we-online.com/SMT-SPACERS