




Dimensions: [mm]













Scale - 2:1

Recommended Land Pattern: [mm]



Product Specific Pinning:



Scale - 2:1

GENERAL TOLERANCE PROJECTION METHOD CHECKED REVISION DATE (YYYY-MM-DD) GE 001.030 2018-10-11 DIN ISO 2768-1m **WIRL-WMB1** Radio module Würth Elektronik eiSos GmbH & Co. KG 169MHz wMBus ORDER CODE EMC & Inductive Solutions WÜRTH Max-Eyth-Str. 1 2607011113000 74638 Waldenburg **ELEKTRONIK** MORE THAN YOU EXPECT Tel. +49 (0) 79 42 945 - 0 BUSINESS UNIT STATUS PAGE www.we-online.com Valid 1/7 eiSmart eiSos@we-online.com

General Properties:

Properties		Test conditions	Value	Unit
Communication Protocol/ Standard	RF _{prot}		wireless M-Bus, EN13757-4, OMS	
Microcontroller	μC MSP430			
Radio Chipset	RF-IC		TI - CC1120	
Memory Size (Flash)			65536	В
Memory Size (RAM)			6144	В
Radio channel min.		wM-BU	SN	
Radio channel max.		wM-BU	SN	
Interface 1	101		UART	
Interface 1 Bitrate Range	IO _{1 Bitrate}	latest FW revision	115.2	kbps
Number of I/O Ports	10 _{Ports}	latest FW revision	6	

Electrical Properties:

Properties		Test conditions	Value		
Operating Supply Voltage Min.	V _{DD min.}	TAMB = 25 °C, RH = 60 %	2	V	
Operating Supply Voltage Max.	V _{DD max.}	TAMB = 25 °C, RH = 60 %	3.6	V	
Recommended Supply Voltage	V _{DD typ}	TAMB = 25 °C, RH = 60 %	3	V	
Supply Current Sleep	I _{sleep}	VDD,typ, TAMB = 25 °C, RH = 60 %	10	μΑ	

Additional General Information:

Ambient Temperature (referring to $I_{\rm R}$)	-40 up to +85 °C				
Operating Temperature	-40 up to +85 °C				
Storage Conditions (in original packaging)	< 40 °C; < 90 % RH				

RF-Electrical Properties:

Properties		Test conditions	Value	Unit
Frequency min.	f _{min.}	VDD,typ, TAMB = 25 °C, RH = 60 %	169.40625	MHz
Frequency max.	f _{max.}	VDD,typ, TAMB = 25 °C, RH = 60 %	169.46875	MHz
Line of Sight Range		Two-ray ground-reflection model	3000	m
Line of Sight Conditions: Antenna Height			2	m
RF Bitrate max.	R _{b, max.}	latest FW revision	4.8	kbps
Supply Current Transmitting	I _{TX}	VDD,typ, TAMB = 25 °C, RH = 60 %	59	mA
Supply Current Receiving	I _{RX}	VDD,typ, TAMB = 25 °C, RH = 60 %	28	mA
Output Power 50 Ohm	P _{Tx, 50 Ω}	TAMB = 25 °C, RH = 60 %	14	dBm
RX sensitivity max.	Rx _{sens, 50 Ω}	50 Ω	-115	dBm
RX sensitivity Condition Bitrate	Rx _{sens, kbps}		2.4	kbps

Product Specific Pinning:

Pin	Pad	Description	1/0		
ANT	1	External antenna connection			
GND	2	Negative supply voltage	Supply		
VCC	3	Positive supply voltage	Supply		
UTXD	4	UART transmit	Output		
URXD	5	UART receive	Input		
/RTS	6	Ready to send signal	Output		
/CTS	7	Clear to send signal	Input		
/DATA_IND	8	see manual for more details	Output		
RESERVED	9	see manual for more details			
RESERVED	10	see manual for more details			
RESERVED	11	see manual for more details			
RESERVED	12	see manual for more details			
MOD_SEL0	13	see manual for more details	Input		
MOD_SEL1	14	see manual for more details	Input		


	-		GE	REVISION 001.030	DATE (YYYY-MM-DD) 2018-10-11	DIN ISO 2768-1m		PROJECTION METHOD	-
	WURTH ELEKTRONIK	Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg		WMB1 F	adio modi us	-	ORDER CODE 2607	7011113000	
1,7-	MORE THAN YOU EXPECT	Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com elSos@we-online.com				BUSINESS UNIT eiSmart	status Valid		PAGE 2/7


Product Specific Pinning:

Pin	Pad	Description	1/0
MOD_SEL2	15	see manual for more details	Input
MOD_SEL3	16	see manual for more details	Input
TEST	17	Testpin - DO NOT CONNECT	
RESERVED	18	see manual for more details	
/RESET	19	Reset-Input	Input
RX_IND	20	Radio activity indicator for reception	Output
TX_IND	21	Radio activity indicator for transmission	Output
RESERVED	22	see manual for more details	
GND	23	Negative supply voltage	Supply



Packaging Specification - Tape and Reel: [mm]







Packaging is refered to the international standard IEC 60286-3:2013

	Таре Туре	A0 (mm)	B0 (mm)	W (mm)	T (mm)	T1 (mm)	T2 (mm)	KO (mm)	P0 (mm)	P1 (mm)	P2 (mm)	DO (mm)	D0 / 2 (mm)	D1 (mm)	d (mm)	E (mm)	S (mm)	F (mm)	Material	Qty. (pcs.)
-		typ.	typ.	±0,3	ref.	max.	typ.	typ.	$\pm 0,1$	$\pm 0,1$	±0,15	+0,1/ -0,0	+0,05/ -0,0	min.	±0,05	$\pm 0,1$	$\pm 0,1$	±0,1		
ı	3	17,60	27,60	44,00	0,35	0,10	4,55	4,10	4,00	24,00	2,00	1,50	0,75	2,00	0,20	1,75	40,40	20,20	Polystyrene	400

Packaging Specification - Reel: [mm]





A (mm)	B (mm)	C (mm)	D (mm)	N (mm)	W1 (mm)	W2 (mm)	W3 (mm)	W3 (mm)	Material	
± 2,0	min.	min.	min.	min.	+ 2,0	max.	min.	max.		
330.00	1.50	12.80	20.20	80.00	44 40	50.40	43.90	47 40	Polysytrene/ Polyurethane	



Further information

Component Libraries:



3D_2607011113000



Altium_WIRL (V9.0)



Eagle_WIRL (V9.0)



Download_IGS_WIRL-WMB1-2607011113001



Download_STP_WIRL-WMB1-2607011113001

Related Products:

- Evaluation Kit: 2607019213001
- USB Radio Stick: 2607046213001

Get a Quote:

Request a quote here!

Tutorials:

- Technical Support
- Manuals
- Software Downloads
- Firmware Individualization
- Certificate of Conformity

Wireless Connectivity & Sensors Overview

REDEXPERT:

REDEXPERT - Range estimation and product comparison

1.7-	MORE THAN YOU EXPECT	eliniary Tel. +49 (t) 79 42 945 - 0 www.we-online.com elSos@we-online.com				BUSINESS UNIT eiSmart	status Valid		PAGE 5/7]
Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 FLEKTRONIK Germany Germany			WIRL-WMB1 Radio module 169MHz wMBus					ORDER CODE 2607011113000		
			GE	001.030	2018-10-11	DIN ISO 2768-1m		METHOD ———] -	

Cautions and Warnings:

The following conditions apply to all goods within the product series of wireless connectivity of Würth Elektronik eiSos GmbH & Co. KG:

General:

- This electronic component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
 equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
 ship control), transportation signal, disaster prevention, medical, public information network, etc. where higher safety and reliability are
 especially required and/or if there is the possibility of direct damage or human injury.
- Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions
 specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
 Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
 sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products also apply to customer specific products.

Product specific:

Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- · All other soldering methods are at the customers' own risk.

Cleaning and Washing:

- Washing agents used during the production to clean the customer application might damage or change the characteristics of the component. Washing agents may have a negative effect on the long-term functionality of the product.
- Using a brush during the cleaning process may break the module. Therefore, we do not recommend using a brush during the PCB cleaning process.

Potting and Coating:

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the component. Expansion could damage components. We recommend a
manual inspection after potting to avoid these effects.

· Conformal coating may affect the product performance.

Storage Conditions:

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- For a moisture sensitive component, the storage condition in the original packaging is defined according to IPC/JEDEC-J-STD-033. It is
 also recommended to return the component to the original moisture proof bag and reseal the moisture proof bag again.
- ESD prevention methods need to be followed for manual handling and processing by machinery.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.

Packaging

 The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

Handling:

- Violation of the technical product specifications such as exceeding the nominal rated current, will void the warranty.
- Violation of the technical product specifications such as but not limited to exceeding the absolute maximum ratings will void the conformance to regulatory requirements.
- The edge castellation is designed and made for prototyping, i.e. hand soldering purposes only.
- Non-antenna modules must be equipped with a proper antenna having specific characteristics.
- The applicable country regulations and specific environmental regulations must be observed.
- Do not disassemble the product. Evidence of tampering will void the warranty.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.

All topics are described in a more detailed manner in the manual for each product.



Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

		CHECKED GE	REVISION 001.030	DATE (YYYY-MM-DD) 2018-10-11	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	-	
WURTH ELEKTRONIK	Würth Elektronik elSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Wattenburg	IUSIVIIIZ WIVIDUS					ORDER CODE 2607011113000		
MORE THAN YOU EXPECT	Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com elSos@we-online.com				BUSINESS UNIT eiSmart	status Valid		PAGE 7/7	