

WÜRTH ELEKTRONIK
MORE THAN YOU EXPECT



QUICK START GUIDE

**Mag1°C Power Module Evaluation
Board for 1710X3801 LGA-12EP**

Evaluation Board 1780X3801

Version 1.0

SCHEMATIC

Features



EN55032
Class B



FIX SS



ADJ. Freq.



PG



UVLO




OCP



OTP



T_s 105 °C



The additional aluminum electrolytic capacitor C1 is only for evaluation board protection purposes. It is mounted at the termination of the supply line and provides slight damping of possible oscillations of the series resonance circuit represented by the inductance of the supply line and the input capacitance. It is not essential for operation.

For accurate V_{IN} and V_{OUT} voltage measurements it is recommended to measure directly at the test pins placed beside the input and output capacitors C2 and C5. It is **not** recommended to use this evaluation board with input and output wire lengths longer than 1 m.

To optimize the EMI performance connect the R_{SW} resistor to V_{IN} to enable spread spectrum behavior.

For the datasheet of the power module visit us at: <https://www.we-online.com/catalog/en/MAGIC-VDLM>



This product is highly sensitive to electrostatic discharge (ESD). As such, always use proper ESD precautions when handling. Failing to follow the aforementioned recommendations can result in severe damage to the part.



WARNING! – Before operating read the attached important notice document!

Ref. Des.	Description Order Code
U1	MagI ³ C Power Module (1710X3801)
C1	Aluminum electrolytic capacitor 220 μ F/50V (865060657012)
CIN	2 x Ceramic chip capacitor 4.7 μ F/50V (885012209048)
CVCC	Ceramic chip capacitor 1 μ F/16V (885012207051)
COUT	2 x Ceramic chip capacitor 47 μ F/16V (885012109011)
C9	Aluminum polymer capacitor 220 μ F/16V (875115350002)
Cf	2 x Ceramic chip capacitor 4.7 μ F/50V (optional) (885012209048)
Lf	Filter inductor, 1 μ H, PD2 (optional) (7447732010)
R1	0 Ω resistor bridge
RENT	not mounted
RENB	not mounted
RPG	1 M Ω
RFBT	402 k Ω
J1	"Jumper for EN connection to either VIN (device enabled) or GND (device disabled) (61301421121)"
J2	Jumper for switching frequency selection. Only one resistor should be selected at a time (61301421121)
J3	Jumper for output voltage selection. Only one resistor should be selected at a time (61301421121)
J4	Jumper to enable & disable spread spectrum behavior (61301421121)


Ref. Des.	Description Order Code
RFBB	Set by jumper
	30.1 k Ω for $V_{OUT} = 12V$ (1A/2A version)
	64.9 k Ω for $V_{OUT} = 6V$ (3A version)
	80.6 k Ω for $V_{OUT} = 5V$
	137 k Ω for $V_{OUT} = 3.3V$
	205 k Ω for $V_{OUT} = 2.5V$
	357 k Ω for $V_{OUT} = 1.8V$ (default setting)
RFSW*	Set by jumper
	976 k Ω for $V_{OUT} = 1.2V$
	open for $V_{OUT} = 0.85V$
	18.2 k Ω for $F_{sw} = 1.5 MHz$ (1A/2A version)
	10 k Ω for $F_{sw} = 1 MHz$ (3A version)
	5.6 k Ω for $F_{sw} = 700 kHz$
	3.3 k Ω for $F_{sw} = 500 kHz$
0 Ω for $F_{sw} = 400 kHz$ (default setting)	
1.8 k Ω for $F_{sw} = 200 kHz$	

**Switching frequency in continuous conduction mode*

For Layout, Gerber and Step files visit us on www.we-online.com/catalog/en/MAGIC-VDLM



OVERVIEW



Description

V_{IN} 3.5 – 38V
 V_{OUT} –0.85V to 6V
at $I_{OUT} = 3A$
–0.85V to 13V
at $I_{OUT} \leq 2.5A$
 I_{OUT} 1A/2A/3A

- 1 VDLM Variable Step Down LGA Module LGA12-EP
- 2 Jumpers (J11) for ENABLE & shut off the Module
- 3 Resistors to set UVLO level
- 4 Jumpers to set predefined output voltage V_{OUT} and fsw
- 5 Jumpers to enable & disable spread spectrum behavior
- 6 Terminal block screw connectors for V_{IN} and V_{OUT}

Absolute maximum ratings

Caution: Exceeding the abs. max. values given in the datasheet may affect the device negatively and may cause permanent damage.

This evaluation board is intended to be operated in a research and development environment under the supervision of qualified technicians and engineers who are trained and experienced in the safe use of electronics. This evaluation board was designed and tested according to CISPR32 Class B standards under Würth Elektronik laboratory test conditions, as indicated in the data sheet of

the corresponding power module. Operation in other test setups may cause unintended electrical behavior and exceed the stated performance and limits imposed by the CISPR32 Class B standards. This evaluation board is not intended for usage in final applications. This evaluation board is not intended for resale.

