Dimensions: [mm]			<b>Electrical Properties:</b>					
			Properties		Value	Unit	Tol.	
			Surface Resistance <sup>1)</sup>	R <sub>S</sub>	0.0005	Ω/ square	typ.	
			Resistance through adhesive		0.003	Ω	typ.	
			Adhesive Thickness		0.03	mm	typ.	
			Adhesive Strength <sup>2)</sup>		4.5	N/ cm	typ.	
			<sup>1)</sup> based on MIL-STD-202F <sup>2)</sup> based on ASTM D1000-10 <b>Certification:</b>			_ <b>.</b>		
			RoHS Approval	Cor		015/0001		
			REACh Approval	_	npliant [2011/65/EU&20			
			Halogen Free	Com	form or declared [(EC)19 Conform [JEDEC JS70			
			Halogen Free		Conform [IEC 61249-2			
			nalogell riee			21]		
25 mm x 33 m								
			General Information:					
$\sim$			Operating Temperature		-25 up to +80 °C			
±i ±i 10 10 10 10 10 10 10 10 10 10 10 10 10			Storage Conditions (in original packaging)		< 40 °C;< 75 % RH			
te 25,0 ±0,25 € flexible copper foil			Moisture Sensitivity Level (MSL)	1				
G flexible copper foil			Flammability: No flame, no glowing. IEC 60695-2-11. Test severity 850°C					
			Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently					
release tape Scale - 1:2								
			CHECKED REVISION DATE (YYYY-M)   IVB 006.001 2023-05-	1	METHOD		୬-	
	WURTH ELEKTRONIK MORE THAN YOU EXPECT	Würth Elektronik eiSes GmbH & Co. KG EMC & Inductive Solutions Max-EyH-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSes@we-online.com	DESCRIPTION					
			WE-CF EMI Shieldin	a Sheet/FN	n			
			Shielding Tape		ORDER CODE		+	
					3003325A			
				BUSINESS UNIT	STATUS		PAGE	
				eiSos	Valid	1	1/2	

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik eiSos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation, transportation electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

# **Important Notes**

# The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

## **1. General Customer Responsibility**

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

## 2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

#### 3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

#### 4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

#### 5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

# 6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

# 7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

#### 8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

ROHS ROHS COMPLANT REACH REACH HALOGEN FREE		CHECKED	REVISION 006.001	DATE (YYYY-MM-DD) 2023-05-08	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	$-\bigcirc$	€-
		WE-CF	WE-CF EMI Shielding Sheet/EMI						
WÜRTH ELEKTRONIK MORE THAN YOU EXPECT	Max-Eyth-Str. 1 74638 Waldenburg	Shielding Tape				ORDER CODE 3003325A			
	Tel. +49 (0) 79 42 945 - 0 T www.we-online.com				BUSINESS UNIT eiSos	status Valid		1	PAGE 2/2

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electronic circuits that require high asteging and reliability functions or performance.