



SOLDER SUFFIX	CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
LF1	Sn96%, Ag4%	Yes	Yes

more than you expect



6C



6D Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

6C

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications	CONVENTION PLACEMENT
6D	9/17	Method: Tape & Reel	6D
6C	3/11	PKG-1028	
		www.we-online.com/midcom	
6B	6/98		
6A	8/97	SEE REVISION SHEET FOR REVISION LEVEL	

Tolerances unless otherwise specified:
Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13]
Fractions: $\pm 1/64$ Footprint: $\pm .005$ [.13]
This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

D.C. RESISTANCE (@20°C): 6-1, 0.171 ohms max. 6D
9-4, 0.093 ohms max.
8-3, 1.630 ohms max.
7-2, 1.630 ohms max.
10-5, 0.220 ohms max. 6D

DIELECTRIC RATING: 500VAC, 1 minute tested by applying 625VAC for 1 second between PRI-SEC.

INDUCTANCE: 32.3uH $\pm 5\%$, 10kHz, 100mVAC, 6-1, Ls.

LEAKAGE INDUCTANCE: 500nH typ., 100kHz, 100mVAC, 6-1(tie 9+4, 8+3, 7+2, 10+6, 1+5), Ls.

6C TURNS RATIO: (1-6):(9-4) = 1.733:1, $\pm 1\%$.
(8-3):(1-6) = 2.62:1, $\pm 1\%$.
(7-2):(1-6) = 2.62:1, $\pm 1\%$.
(1-6):(10-5) = 1:1, $\pm 1\%$.

6C OPERATING TEMPERATURE RANGE: -40°C to +125°C including temp rise.

TRANSFORMER INFORMATION:

Pout max.: 9.00W
Pout min.: 4.90W
Estimated Temp. Rise @ Pout max.: 40.0°C
Estimated Efficiency: 78.1%
Estimated Maximum Duty Cycle: 39.7%

SWITCH SELECTION INFORMATION

Input Voltage Range: 16 - 40V
Peak Current: 2.836A
Vsw @ Rated Output Voltages: 50 + (Vmax - 40)
Operating Frequency: 100k - 250kHz

Transformer will operate in Discontinuous Mode below Minimum Specified Output Voltage of Pout Min. Pout min. varies with frequency of switcher (from 100 to 250kHz)
Pout Min = 490.0/(Frequency in kHz) Watts.

DRAWING TITLE
TRANSFORMER

eiSos p/n: 750030405

PART NO.

30405R-LF1



SPECIFICATION SHEET 1 OF 1

6C