#### **Dimensions: [mm] Recommended Hole Pattern: [mm]** Щ Щ 12 11 63,51 ±0.25 □ 0,50 ±0.15 ±0.25 13,72 ±0.15 1,02 ±0.15 9,14 ±0.15 0,55 ±0.25 7,14 ±0.15 13,25 1,78 ±0.15 2,03 ±0.15 $0,29 \pm 0.25$ 63,75 ±0.25 0,51 ±0.15 <sup>10</sup>9 ∠LED1 12 ±0,2 2,86 01802015 3.20 x 1,90 ±0.15 $1,19 \pm 0.25$ 3,43 ±0.15 4,32 ±0.15 10,16 ±0.15 9,14 ±0.15 15,75 ±0.1 15,75 ±0.1 15,75 ±0. 47,25 ±0.25 Ø 3,50 ±0.1 59,95 ±0.25 7,14 ±0.15 2,54 ±0.15 59,95 ±0.25 3,43 ±0.15 4,32 ±0.15 5,75 ±0.20 5,59 ±0.15 9,14 ±0.15 10,16 ±0.15 1,19 ±0.25 Scale - 1:1 Scale - 1:1 GENERAL TOLERANCE PROJECTION METHOD CHECKED REVISION DATE (YYYY-MM-DD) BBo 001.002 2022-08-05 DIN ISO 2768-1m RoHS COMPLIANT REACH COMPLIANT **WR-MJ Modular Jack Tab Up** Würth Elektronik eiSos GmbH & Co. KG ORDER CODE EMC & Inductive Solutions WÜRTH Max-Eyth-Str. 1 615032137921 74638 Waldenburg **ELEKTRONIK**

Tel. +49 (0) 79 42 945 - 0

www.we-online.com

eiSos@we-online.com

BUSINESS UNIT

eiCan

Horizontal Shielded, Ganged 4 Ports with LED & EMI

Panel Finger 8P8C

STATUS

Valid

PAGE

1/7

MORE THAN YOU EXPECT

# **Article Properties:**

Number of Pins (xPxC)	8P8C
-----------------------	------

# **Kind Properties:**

Durability	500 Mating cycles
LED (Left-Right)	yellow-green

# **Material Properties:**

Insulator Material	PBT					
Insulator Flammability Rating	UL94 V-0					
Insulator Color	Black					
Contact Material	Copper Alloy					
Contact Plating	Selective Gold					
Contact Type	Stamped					
Shielding Material	Bronze					
Shielding Plating	Nickel (Ni)					

### **General Information:**

Operating Temperature	-40 up to +85 °C
3 1 1	

# **Electrical Properties:**


Properties		Test conditions	Value	Unit	Tol.
Working Voltage			120	V (AC)	
Withstanding Voltage		1 min	1000	V (AC)	
Withstanding Voltage Shielding to Pin		1 min	1500	V (AC)	
Contact Resistance	R		20	mΩ	max.
Insulation Resistance	R <sub>ISO</sub>		500	ΜΩ	min.

# **Certification:**


RoHS Approval	Compliant [2011/65/EU&2015/863]				
REACh Approval Conform or declared [(EC)1907/2006]					
UL Approval	E324776				

	REACH COMMANDATE COMMANDATE		BB0	nevision 001.002	DATE (YYYY-MM-DD) 2022-08-05	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	<b>-</b>		
			WR-M.	I Modul	ar Jack Ta	h IIn					
	Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 FLEKTRONIK Germany Germany			modul	ar odok ra	БОР	ORDER CODE	032137921			
	MOR	E THAN EXPECT	Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	SIZE/TYPE Horizontal Shiel Panel Finger 8F		Ports with LED & EMI	BUSINESS UNIT eiCan	status Valid		PAGE 2/7	


# Packaging Specification - Tray: [mm]




L <sub>TRA</sub> (mm)	L1 <sub>TRA</sub> (mm)	L2 <sub>TRA</sub> (mm)	W <sub>TRA</sub> (mm)	W1 <sub>TRA</sub> (mm)	W2 <sub>TRA</sub> (mm)	H <sub>TRA</sub> (mm)	Packaging Unit	Material
typ.	typ.	typ.	typ.	typ.	typ.	typ.	pcs.	
240	137.8	60	100	1//3	23	21	21	Plactic




# Packaging Specification - Tray and Carton: [mm]



L <sub>C</sub> (mm)	W <sub>C</sub> (mm)	H <sub>C</sub> (mm)	No. of tray	Packaging Unit	Material
typ.	typ.	typ.	tra.	pcs.	
455	365	270	35	735	Paner



# **Classification Wave Soldering Profile:**



# **Classification Wave Soldering Profile:**

Profile Feature		Pb-Free Assembly	Sn-Pb Assembly		
Preheat Temperature Min	T <sub>s min</sub>	100 °C	100 °C		
Preheat Temperature Typical	T <sub>s typical</sub>	120 °C	120 °C		
Preheat Temperature Max	T <sub>s max</sub>	130 °C	130 °C		
Preheat Time $t_s$ from $T_{s min}$ to $T_{s max}$	t <sub>s</sub>	70 seconds	70 seconds		
Ramp-up Rate	ΔΤ	150 °C max.	150 °C max.		
Peak Temperature	T <sub>p</sub>	250 °C - 260 °C	235 °C - 260 °C		
Time of actual peak temperature	t <sub>p</sub>	max. 10 seconds max. 5 seconds each wave	max. 10 seconds max. 5 seconds each wave		
Ramp-down Rate, Min		~ 2 K/ second	~ 2 K/ second		
Ramp-down Rate, Typical		~ 3.5 K/ second	~ 3.5 K/ second		
Ramp-down Rate, Max		~ 5 K/ second	~ 5 K/ second		
Time 25 °C to 25 °C		4 minutes	4 minutes		

refer to EN61760-1:2006

REACH REACH COMPANIANT		CHECKED BB0	REVISION 001.002	DATE (YYYY-MM-DD) 2022-08-05	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	<del> </del>
		WR-MJ Modular Jack Tab Up						
Würth ELEKTRINIK eißos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 7-4638 Waldenburg Germany						ORDER CODE	32137921	
MORE THAN YOU EXPECT	Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	SIZE/TYPE Horizontal Shie Panel Finger 8		Ports with LED & EMI	BUSINESS UNIT eiCan	status Valid		PAGE 5/7

### **Cautions and Warnings:**

# The following conditions apply to all goods within the product series of the Connectors of Würth Elektronik eiSos GmbH & Co. KG:

#### General:

- This mechanical component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
  equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
  ship control), transportation signal, disaster prevention, medical, public information network, etc. where higher safety and reliability are
  especially required and/or if there is the possibility of direct damage or human injury.
- Mechanical components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The mechanical component is designed and manufactured to be used within the datasheet specified values. If the usage and operation
  conditions specified in the datasheet are not met, the component may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged.
- Prevent any damage or scratches on the component, especially on the actuator.
- Direct mechanical impact to the product shall be prevented (e.g overlapping of the PCB's).
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
  Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
  sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products do also apply to customer specific products.
- The mechanical component is designed to be used along with Würth Elektronik counterparts and tools. Würth Elektronik cannot ensure the reliability of these components while being used with other products.

### **Product Specific:**

### Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- All other soldering methods are at the customers' own risk.

#### **Cleaning and Washing:**

- Washing agents used during the production to clean the customer application might damage or change the characteristics of the component, body, pins and termination. Washing agents may have a negative effect on the long-term functionality of the product.
- Using a brush during the cleaning process may deform function relevant areas. Therefore, we do not recommend using a brush during the PCB cleaning process.

### **Potting and Coating:**

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the components. Expansion could damage the components. We
recommend a manual inspection after potting or coating to avoid these effects.

### **Storage Conditions:**

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer
  degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of
  shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.


### Packaging:

• The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

### **Handling:**

- Do not repeatedly operate the component with excessive force. It may damage or deform the component resulting in malfunction.
- In the case a product requires particular handling precautions, in addition to the general recommendations mentioned here before, these
  will appear on the product datasheet.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.



### **Important Notes**

# The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

### 1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

### 2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

#### 3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

#### 4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

#### 5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

### 6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

### 7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

#### 8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

