


# **Dimensions: [mm]**







# **Recommended Panel Cutout: [mm]**



## **Article Properties:**

| Properties           |   | Value | Unit | Tol. |
|----------------------|---|-------|------|------|
| Nominal Cable Length | L | 200   | mm   | ±2mm |
| Panel Thickness      |   | 2.8   | mm   | max. |

| 1 | <b>③</b>          | 0                  |
|---|-------------------|--------------------|
| 7 | RoHS<br>COMPLIANT | REACH<br>COMPLIANT |

Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg

Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com

| DATE (YYYY-MM-DD) |
|-------------------|
| 2020-10-27        |

GENERAL TOLERANCE DIN ISO 2768-1m

**WR-UMRF SMA Bulkhead Jack to UMRF Right Angle Plug** 

636207100200

CHECKED

JTs

Coaxial Cable Dia. 1.37mm Black Jacket

REVISION

001.000

BUSINESS UNIT eiCan

STATUS PAGE Valid 1/6

## **Material Properties Cable:**

| Properties                   | Value | Unit |
|------------------------------|-------|------|
| Nominal Outer Cable Diameter | 1.37  | mm   |
| Cable Jacket Material        | FEP   |      |
| Cable Flammability Rating    | VW-1  |      |
| Cable Jacket Color           | Black |      |

## **Material Properties Connector 1:**

| Insulator Material        | PTFE             |
|---------------------------|------------------|
| Insulator Color           | White            |
| Center Contact Material   | Beryllium Copper |
| Center Contact Plating    | Gold over Nickel |
| Body Material             | Brass            |
| Body Plating              | Gold over Nickel |
| Spacer Material           | Brass            |
| Spacer Plating            | Gold over Nickel |
| Nut Material              | Brass            |
| Nut Plating               | Gold over Nickel |
| Lock Washer Material      | Brass            |
| Lock Washer Plating       | Gold over Nickel |
| Heat Shrink Tube Material | PE               |
| Heat Shrink Tube Color    | Black            |

## **Material Properties Connector 2:**

| Insulator Material            | PA66             |
|-------------------------------|------------------|
| Insulator Flammability Rating | UL94 V-0         |
| Insulator Color               | White            |
| Contact Material              | Phosphor Bronze  |
| Contact Plating               | Gold over Nickel |
| Shell Material                | Phosphor Bronze  |

# **Material Properties Connector 2:**

| Shell Plating | Gold over Nickel |
|---------------|------------------|
|---------------|------------------|

# **Kind Properties:**

| Properties         |     | Value       |  |  |  |  |
|--------------------|-----|-------------|--|--|--|--|
| Interface 1        | 101 | MIL-STD-348 |  |  |  |  |
| Connector Type 1   |     | SMA         |  |  |  |  |
| Orientation Type 1 |     | Straight    |  |  |  |  |
| Gender 1           |     | Jack        |  |  |  |  |
| Connector Type 2   |     | UMRF        |  |  |  |  |
| Orientation Type 2 |     | Right Angle |  |  |  |  |
| Gender 2           |     | Plug        |  |  |  |  |

# **General Properties:**

| Operating Temperature | -40 up to +90 °C |
|-----------------------|------------------|
| operaning remperature | 10 49 10 100 0   |

# **Electrical Properties:**

| Properties Test conditions                                    |   | Value    | Unit    | Tol. |      |
|---|---|----------|---------|------|------|
| Impedance   | Z | DC~6 GHz | 50      | Ω    |      |
| Frequency Range f   |   | DC~6 GHz |         |      |      |
| VSWR DC~6 GHz   |   | 1.6      |         | max. |      |
| Insertion Loss IL DC~6 GHz                                    |   | DC~6 GHz | 1.5     | dB   | max. |
| Insulation Resistance R <sub>ISO</sub> 100 V (DC) in 120 sec. |   | 500      | МΩ      | min. |      |
| Withstanding Voltage 200 V (AC) in 60 sec.                    |   | 200      | V (RMS) | min. |      |

# **Mechanical Properties:**

| Properties              | Test conditions | Value | Unit   | Tol. |
|-------------------------|-----------------|-------|--------|------|
| Mating Cycle            | Connector 1     | 500   | Cycles |      |
| Mating Cycle            | Connector 2     | 30    | Cycles |      |
| Un-Mating Force Initial | Connector 2     | 5     | N      | min. |

|                          |   | JTs                          | REVISION<br>001.000 | DATE (YYYY-MM-DD)<br>2020-10-27 | GENERAL TOLERANCE DIN ISO 2768-1m |                 | PROJECTION<br>METHOD |     | <b>-</b>    |
|--------------------------|---|------------------------------|---------------------|---------------------------------|-----------------------------------|-----------------|----------------------|-----|-------------|
| ROHS COMPLIANT COMPLIANT |   | WR-UMRF SMA Bulkhead Jack to |                     |                                 |                                   |                 |                      |     |             |
|                          | Würth Elektronik eiSos GmbH & Co. KG<br>EMC & Inductive Solutions<br>Max-Eyth-Str. 1<br>74638 Waldenburg<br>Germany | UMRF                         | Right Aı            | ngle Plug                       |                                   | 0RDER CODE 6362 | 2071002              | :00 |             |
| WÜRTH ELEKTRONIK         | Tel. +49 (0) 79 42 945 - 0<br>www.we-online.com<br>elSos@we-online.com  | SIZE/TYPE  Coaxial Cable     | Dia. 1.37mm Blad    | ck Jacket                       | eiCan                             | status<br>Valid |                      | - 1 | PAGE<br>2/6 |

## **Mechanical Properties:**

| Properties                              | Test conditions          | Value | Unit | Tol. |
|---|--------------------------|-------|------|------|
| Un-Mating Force After Test              | Connector 2              | 3     | N    | min. |
| Cable Pull Force-Axial 1)               | Connector 2              | 4     | N    | max. |
| Cable Pull Force-Vertical <sup>2)</sup> | Connector 2              | 2     | N    | max. |
| Crimping Force                          | Connector 2              | 15    | N    | min. |
| Cable Retention                         | Retention Connector 1 22 |       | N    | min. |
| Min. Bend Radius                        |                          | 4     | mm   |      |


## **Certification:**


| RoHS Approval  | Compliant [2011/65/EU&2015/863]     |  |  |
|----------------|-------------------------------------|--|--|
| REACh Approval | Conform or declared [(EC)1907/2006] |  |  |

## **Specific Recommendation:**

| General Information In order to handle products correctly, please download our precaution of under "Downloads" on our Homepage: www.we-online.com/precau |
|--|
|--|


## **Typical Attenuation:**






<sup>1)</sup> After mated with the receptacle, and no electrical discontinuity of 1 micro-sec. min. 2) After mated with the receptacle, and no electrical discontinuity of 1 micro-sec. min.

# Packaging Specification - Carton: [mm]



| L <sub>C</sub> (mm) | W <sub>C</sub> (mm) | H <sub>C</sub> (mm) | No. Piece(s) in<br>Bag1 | No. Pieces in<br>Bag2 | No. of paperboard | Packaging<br>Unit | Material |
|---------------------|---------------------|---------------------|-------------------------|-----------------------|-------------------|-------------------|----------|
| typ.                | typ.                | typ.                | pcs.                    | pcs.                  | pcs.              | pcs.              |          |
| 270                 | 330                 | 240                 | 20                      | n                     | 1                 | 1200              | Danor    |



## **Cautions and Warnings:**

# The following conditions apply to all goods within the product series of the Connectors of Würth Elektronik eiSos GmbH & Co. KG:

#### General:

- This mechanical component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
  equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
  ship control), transportation signal, disaster prevention, medical, public information network, etc. where higher safety and reliability are
  especially required and/or if there is the possibility of direct damage or human injury.
- Mechanical components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The mechanical component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions specified in the datasheet are not met, the component may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged.
- Prevent any damage or scratches on the component, especially on the actuator.
- Direct mechanical impact to the product shall be prevented (e.g overlapping of the PCB's).
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
  Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
  sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products do also apply to customer specific products.
- The mechanical component is designed to be used along with Würth Elektronik counterparts and tools. Würth Elektronik cannot ensure
  the reliability of these components while being used with other products.

## **Product Specific:**

## Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- All other soldering methods are at the customers' own risk.

#### **Cleaning and Washing:**

- Washing agents used during the production to clean the customer application might damage or change the characteristics of the component, body, pins and termination. Washing agents may have a negative effect on the long-term functionality of the product.
- Using a brush during the cleaning process may deform function relevant areas. Therefore, we do not recommend using a brush during the PCB cleaning process.

## **Potting and Coating:**

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the components. Expansion could damage the components. We
recommend a manual inspection after potting or coating to avoid these effects.


### **Storage Conditions:**

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer
  degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of
  shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.

## **Handling:**

- Do not repeatedly operate the component with excessive force. It may damage or deform the component resulting in malfunction.
- In the case a product requires particular handling precautions, in addition to the general recommendations mentioned here before, these
  will appear on the product datasheet.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.



## **Important Notes**

# The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

#### 1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

## 2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

#### 3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

#### 4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

#### 5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

#### 6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

### 7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

#### 8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

