

Article Properties:

Properties		Value	Unit	Tol.
Nominal Cable Length	L	152.4	mm	±2mm
Panel Thickness		2.8	mm	max.



GÐ

RoHS COMPLIANT

REACh COMPLIANT

Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com

CHECKED JaC	REVISION 001.000	DATE (YYYY-MM-DD) 2020-04-30	general tolerance DIN ISO 2768-1m		PROJECTION METHOD	
		IA Bulkhea ngle Plug	ORDER CODI	019105	15301	
SIZE/TYPE			BUSINESS UNIT	STATUS		PAGE


Valid

1/6

eiCan

Recommended Panel Cutout: [mm]

Flexible Cable RG-316/U



This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard and rel

Material Properties Cable:

Properties	Value			
Cable	RG-316/U			
Nominal Outer Cable Diameter	2.49	mm		

Material Properties Connector 1:

Insulator Material	PTFE			
Insulator Color	White			
Center Contact Material	Beryllium Copper			
Center Contact Plating	Gold, min. 0.076µm over Nickel			
Body Material	Brass			
Body Plating	Gold, min. 0.076µm over Nickel			
Ferrule Material	Brass			
Ferrule Plating	Gold, min. 0.076µm over Nickel			
Nut Material	Brass			
Nut Plating	Gold, min. 0.076µm over Nickel			
Lock Washer Material	Brass			
Lock Washer Plating	Gold, min. 0.076µm over Nickel			
Heat Shrink Tube Material	PE			
Heat Shrink Tube Color	Black			

Material Properties Connector 2:

Insulator Material	PTFE			
Insulator Color	White			
Center Contact Material	Brass			
Center Contact Plating	Gold, min. 0.076µm over Nickel			
Body Material	Brass			
Body Plating	Gold, min. 0.076µm over Nickel			
Snap Ring Material	Beryllium Copper			
Snap Ring Plating	Gold, min. 0.076µm over Nickel			
		1.1		

Material Properties Connector 2:

Cover Material	Brass
Cover Plating	Gold, min. 0.076µm over Nickel
Ferrule Material	Brass
Ferrule Plating	Gold, min. 0.076µm over Nickel
Heat Shrink Tube Material	PE
Heat Shrink Tube Color	Black

Kind Properties:

Properties		Value				
Interface 2	102	IEC 61169-52				
Cable Type		Flexible				
Cable Shielding		Braid				
Connector Type 1		SMA				
Gender 1		Jack Straight				
Orientation Type 1						
Connector Type 2		MMCX				
Gender 2		Plug				
Orientation Type 2		Right Angle				

General Information:

Operating Temperature	-55 up to +155 °C

Electrical Properties:

	Properties		Test conditions	Value	Unit	Tol.
	Impedance	Z	DC~6 GHz	50	Ω	
	Frequency Range	f		DC~6 GHz		
	VSWR		DC~6 GHz	1.5		max.
	Insertion Loss	IL	DC~6 GHz	1	dB	max.
	Insulation Resistance	R _{ISO}	500 V (DC) in 120 sec.	1000	MΩ	min.

	ROME LANT REACH COMPLIANT COMPLIANT		CHECKED	REVISION 001.000	DATE (YYYY-MM-DD) 2020-04-30	GENERAL TOLERANCE DIN ISO 2768-1m	PROJECTI METHOD) -
			-			ad Jack to	3		
		ELEKTRONIK 74638 Waldenburg		Right A	ngle Plug		ORDER CODE	10515301	I
	MORE THAN YOU EXPECT	Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	SIZE/TYPE Flexible Cable	RG-316/U		BUSINESS UNIT eiCan	status Valid		PAGE 2/6

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wirth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektronik elSos GmbH & Co KG must be information network etc.. Worth Elektr

Electrical Properties:

Properties		Test conditions	Value		Tol.
Withstanding Voltage		500 V (AC) in 60 sec.	500	V (RMS)	min.


Mechanical Properties:

Properties	Value	Unit	Tol.
Center Contact Retention (Axial)	26.7	N	min.
Center Contact Retention (Axial)	10	N	min.
Mating Cycle	500	Cycles	
Force to Engage ³⁾	18	Ν	max.
Force to Disengage ⁴⁾	6	Ν	min.
Recommended Mating Torque ⁵⁾	57	N*cm	
Min. Bend Radius	12.7	mm	
Cable Retention	44.5	Ν	min.

¹⁾ Connector Type 1
 ²⁾ Connector Type 2
 ³⁾ Connector Type 2
 ⁴⁾ Connector Type 2
 ⁵⁾ Connector Type 1

Certification:

RoHS Approval	Compliant [2011/65/EU&2015/863]
REACh Approval	Conform or declared [(EC)1907/2006]



This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be information intended for use in equipment where a higher safety standard and reliability standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be information intended for use in equivalent is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Wurth Elektronik elSos GmbH & Co KG must be information network etc.. Wurth Elektronik elSos GmbH & Co KG must be information intended to use is electronic component which is used in electrical circuits there adjust high standard is especially executed an electronic component which is used in electrical circuits there are electrical circuits ther

F

RoHS COMPLIANT

		N°C -		H _c					
L _C (mm) W _C (<u>typ.</u> typ. 420 225	mm) H _C (mm) typ. 270	No. Pieces in Bag pcs. 10	No. of paperboardPackaging Unitpcs.pcs.11000	Material Paper					
			Reach Compliant Reach Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Compliant Reach Co	Würth Elektronik elSos GmbH & Co. KG EMC & Inductive Solutions Max EyHr JSr. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com elSos@we-online.com	JaC 00 DESCRIPTION WR-CXAS	SION DATE (YYYYAMA-DD) 2020-04-30 SY SMA Bulkhe ight Angle Plug	a	PROJECTION METHOD ORDER CODE 655019105 STATUS Valid	515301 PAGE 4/6

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation ignal, disaster prevention, medical, public information network etc.. Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

Cautions and Warnings:

The following conditions apply to all goods within the product series of the Connectors of Würth Elektronik eiSos GmbH & Co. KG:

General:

- This mechanical component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
 equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
 ship control), transportation signal, disaster prevention, medical, public information network, etc. where higher safety and reliability are
 especially required and/or if there is the possibility of direct damage or human injury.
- · Mechanical components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The mechanical component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions specified in the datasheet are not met, the component may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged.
- Prevent any damage or scratches on the component, especially on the actuator.
- Direct mechanical impact to the product shall be prevented (e.g overlapping of the PCB's).
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
 Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
 sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the
 authority of the customer. All technical specifications for standard products do also apply to customer specific products.
- The mechanical component is designed to be used along with Würth Elektronik counterparts and tools. Würth Elektronik cannot ensure
 the reliability of these components while being used with other products.

Product Specific:

Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- · All other soldering methods are at the customers' own risk.

Cleaning and Washing:

- Washing agents used during the production to clean the customer application might damage or change the characteristics of the component, body, pins and termination. Washing agents may have a negative effect on the long-term functionality of the product.
- Using a brush during the cleaning process may deform function relevant areas. Therefore, we do not recommend using a brush during the PCB cleaning process.

Potting and Coating:

• If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking could lead to an incomplete seal, allowing contaminants into the components. Expansion could damage the components. We recommend a manual inspection after potting or coating to avoid these effects.

Storage Conditions:

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of shipment.
- · Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.

Packaging:

• The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

Handling:

- Do not repeatedly operate the component with excessive force. It may damage or deform the component resulting in malfunction.
- In the case a product requires particular handling precautions, in addition to the general recommendations mentioned here before, these
 will appear on the product datasheet.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.

				CHECKED REVISION DATE (YYY-MM-0D) GENERAL TOLERANCE JaC 001.000 2020-04-30 DIN ISO 2768-1m				PROJECTION METHOD	-	€-
	Würth Elektronik elSas GmbH & Co. KG EMC & Inductive Solutions WURTH Max-Eyth-Str. 1 ELEKTRONIK 74638 Waldenburg		WR-CXASY SMA Bulkhead Jack to							
			MMCX	MMCX Right Angle Plug				ORDER CODE 65501910515301		
	YOU EXPE	AIN Tel. +49 (0) 79 42 945 - 0	SIZE/TYPE Flexible Cable	RG-316/U		BUSINESS UNIT eiCan	status Valid			page 5/6

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in areas such as military, aerospace, aviation, nuclear control, ship control, ship control, train control, tra

Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

				CHECKED	REVISION 001.000	DATE (YYYY-MM-DD) 2020-04-30	general tolerance DIN ISO 2768-1m		PROJECTION METHOD	 ⊕-
			-	WR-CXASY SMA Bulkhead Jack to						
			Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany	MMCX	Right A	ngle Plug	ORDER CODE 65501910515301			
	./5	MORE THAN YOU EXPECT	Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com	SIZE/TYPE Flexible Cable	RG-316/U		BUSINESS UNIT eiCan	status Valid		PAGE 6/6

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG must be informed on every electronic component which is used in effective directive di