
	A
4.37 OPERATING TEMPERATURE: -40 UP TO 105°C 1.20 Image: Complexity of the second s	
COMPLIANCE: LEAD FREE AND ROHS LECTRICAL CURRENT RATING: 5 A WORKING VOLTAGE: 250 VAC INSULATOR RESISTANCE: >1000 MOHM DIELECTRIC WITHSTANDING VOLTAGE: 1500 VAC/MN CONTACT RESISTANCE: 10 mOHM MAX STANDARD CERTIFIED: E323964 SOLDERING	
	В
$\begin{array}{c} \hline \\ \hline $	С
RoHS Compliant PROJECTION: Seneral TOLERANCE X = $^{+}/_{-} 0.2$ XX = $^{+}/_{-} 0.15$	
APPROVAL: BBu UNIT: MM DESCRIPTION: 3.00MM SMT SINGLE ROW MALE RIGHT ANGLED HEADER SIZE	
H 02-JUN-16 TPK AK REV DATE FILE BY	+



1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	oHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE	O		1
F					.X = ⁺ /_ 0.2			
E					.XX = ⁺ /_ 0.15			
D						WÜRTH ELEKTRONĪK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	D
В					SCALE:			Р
A	10-SEP-14	PDF	QL]	SHEET: 3/3	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			