					4	5		
5,3	2,6 2,6 2,6 2,54 2,54 10,	B ±0,3	 	Ø 1,5 1,5 2,54 10,16 A ±0 PCB LAYOUT - COM		ERISTICS 3: UL94V0 PER ALLOY / Ni+Sn EEL / Zn R ALLOY / Ni+Sn TURE: -30°C UP TO +120°C REE AND ROHS UL VDE 16A 24A 300VAC 750VAC GE: 1,6KV 3KV E: 20 mΩ MAX 131 CAT. N°: MRT15 (4) 450 TYPE: MRT15 0-12 AWG / 0,05-3,31 mm ² 5Lb.In / 0,5 Nm		В
<u> </u>	Compliant				wire stripe length SCREW: M3 PITCH: 10,16 mm SOLDERING JEDEC LEAD FREE WA PACKAGING BOX			С
G F E D				GENERAL TOLERANCE ±0,1				L
С			APPROVAL: QL	UNIT: MM	DESCRIPTION: SERIE 2446 - 10.16 MM - VER	RTICAL CABLE ENTRY WITH	SIZE	1
В	00 11 11 12			SCALE:	RISING CAGE CLAMP - WR-TBL		A4	15
A REV		PDF AK FILE BY		SHEET: 1/2 DRAW: AK	WERI PART NO: 691 244 600 0xx			

1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	oHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE]
F					.X = ⁺ /_ 0.2			
E					.XX = ⁺ /_ 0.15			
D						WÜRTH ELEKTRONĬK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	lD
В]	SCALE:			٢
A	10-SEP-14	PDF	QL	1	SHEET: 2/2	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			