1		2	3	4	5	
A±0	3.5±0.3	0.8±0.1	0.3 0.3 		G: UL94-V0 IGE ESS STEEL S: TIN ATURE: -40°C UP TO 115°C REE AND ROHS CULUS 6A 150 VAC AGE: 2.0 KV E: 20 mΩ max	В
2.54±0.2	2.54±0.1	3±0.3	5.08±0.2	WIRE STRIPE LENGTH PITCH: 2.54 MM SOLDERING: JEDEC LEAD FREE WA PACKAGING BOX DIMENSION A = 2.54 x NB PINS + 2.	AVE SOLDERING PROCESS	С
C 12-NOV-14 GEI	NERAL UPDATE	AK AS GG BY	GENERAL TOLERANCE .X = <sup>+</sup> /_ 0.2 .XX = <sup>+</sup> /_ 0.15 UNIT: MM SCALE: SHEET: 1/2 DRAW: AS	WÜRTH ELEKTRONIK DESCRIPTION: SERIE 4039 B - 2.54MM SCF - WR-TBL WERI PART NO: 691 403 900 0xx B	REWLESS VERTICAL ENTRY	יין

1	2	3	4	5	-
					_

А

В

С

## **Cautions and Warnings:**

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	toHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE			1
F					.X = <sup>+</sup> /_ 0.2			
E					.XX = <sup>+</sup> /_ 0.15			
D						WÜRTH ELEKTRONĪK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	ld
В				]	SCALE:			٢
A	10-SEP-14	PDF	QL	]	SHEET: 2/2	WERI PART NO: DISCLAIMER	<b>A4</b>	
REV	DATE	FILE	BY		DRAW: QL			