	1		2		3		4	5		
				- 12.5 ±0.3 -		Pitch:3.81mm Poles A(mm) 2 8.42 3 12.23 4 16.04 5 19.85 6 23.66 7 27.47 8 31.28 9 35.09 10 38.90 11 42.71 12 46.52 14 54.14	TECHNICAL CHARACTER MATERIAL INSULATOR: PA 66 FLAMABILITY RATING: U COLOR: GREEN & ORAN METAL SPRING: STAINLE WIRE GUARD: PhBz TIN I ENVIRONMENTAL OPERATING TEMPERATU COMPLIANCE: LEAD FRE ELECTRICAL CURRENT RATING: WORKING VOLTAGE: WITHSTANDING VOLTAGE CONTACT RESISTANCE: STANDARD SALS CERTIFIED E31541 MECHANICAL SOLID WIRE: STRANDED WIRE: WIRE STRIPE LENGTH: S PITCH: 3.81 MM PACKAGING BOX	294-V0 GE ISS STRIP STEEL PLATED JRE: -40 UP TO 115°C IE AND ROHS CULUS 8A 300VAC E: 2.0KV 20 mOhm max 4 28-16 AWG / 0.081-1.31 M 28-16 AWG / 0.081-1.31 M		В
Rol	3.81 ±0.1				5.8 ±0.2					
G F				PROJECTION:	GENERAL TOL					
E		+ +			+ 1	+/_ 0.2				Η
D				1	= XX.	+/_ 0.15				
С	01-FEB-17	UPDATE	ES	APPROVAL: RJ	UNIT: MM		DESCRIPTION: SERIE 368B - 3.81MM Scewless	Vertical Cable Entry Plug	SIZE	Ы
В	02-JUL-13	STANDARD POLES	QL	1	SCALE:					ח
		PDF	GG	1	SHEET: 1/2		WERI PART NO: 691 368 300 0xx B		A	
A	20-JUN-12	101	99		SHEET: 1/2	I	WERT FART NO. 031 300 300 000 D			

1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	oHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE]
F					.X = ⁺ /_ 0.2			
E					.XX = ⁺ /_ 0.15			
D						WÜRTH ELEKTRONĬK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	lD
В]	SCALE:			٢
A	10-SEP-14	PDF	QL	1	SHEET: 2/2	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			