| | 1 | | 2 | | | 3 | | 4 | 5 | | \Box |
|---------------|---------------|----------------|------|---------------|-----|---|---------------|--|---|------------|--------|
| 0,8= 5,2±1 | 0.3 | €.08±0.2 | Ø1.5 | | | Pitch : 2.54mm Poles A(mm) Poles 2 7.62 15 3 10.16 16 4 12.70 17 5 15.24 18 6 17.78 19 7 20.32 20 8 22.86 21 9 25.40 22 10 27.94 23 11 30.48 24 12 33.02 25 13 35.56 14 | | TECHNICAL CHARACTERIS MATERIAL INSULATOR: PA66 FLAMMABILITY RATING: UL: COLOR: GREEN/ORANGE WIRE GUARD: STAINLESS S CONTACT: BRASS SOLDER TAIL PLATING: TIN ENVIRONMENTAL OPERATING TEMPERATURI COMPLIANCE: LEAD FREE ELECTRICAL CURRENT RATING: WORKING VOLTAGE: WITHSTANDING VOLTAGE: ONTACT RESISTANCE: STANDARD Mus CERTIFIED E315414 MECHANICAL SOLID WIRE: STRANDED WIRE: WIRE STRIPE LENGTH: 9-10 PITCH: 2.54 MM SOLDERING: JEDEC LEAD FREE WAVE S PACKAGING: BOX | 94-V0 STEEL E: -40°C UP TO 115°C AND ROHS cULus 6A 150VAC 2.0KV 20 mΩ MAX 26-20 AWG / 0.129-0.518 MM 26-20 AWG / 0.129-0.518 MM | | A B |
| G | oHS Compliant | | | PROJECTION: | GEN | ERAL TOLERANCE | | O- | | | - |
| F | | | | | | .X = ⁺ /_ 0.2 | | | | | |
| E | | | | | | .XX = ⁺ /_ 0.15 | | | | | |
| D | | | | | | | WÜRTH ELEK | | | | _ |
| С | 04-OCT-14 | GENERAL UPDATE | | APPROVAL: FBr | | : MM | | SERIE 4029 B - 2.54MM SCREV | VLESS HORIZONTAL ENTRY | SIZE | D |
| В | 24-SEP-13 | DWG REVIEW | QL | | SCA | | - WR-TBL | | | | |
| A | 02-JUL-12 | PDF | GG | | | ET: 1/2 | WERI PART NO: | 691 402 910 0xx B | | A4 | |
| REV | DATE | FILE | BY | | DRA | W: AS | | | | | |

| 1 | 2 | 3 | 4 | 5 | - |
|---|---|---|---|---|---|
| | | | | | _ |

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

| R | toHS Compliant | | | | | | | |
|-----|----------------|------|----|--------------|----------------------------|--------------------------|-----------|----|
| G | | | | PROJECTION: | GENERAL TOLERANCE | | | 1 |
| F | | | | | .X = ⁺ /_ 0.2 | | | |
| E | | | | | .XX = ⁺ /_ 0.15 | | | |
| D | | | | | | WÜRTH ELEKTRONĪK | | |
| С | | | | APPROVAL: JC | UNIT: MM | DESCRIPTION: DISCLAIMER | SIZE | ld |
| В | | | |] | SCALE: | | | ٢ |
| A | 10-SEP-14 | PDF | QL |] | SHEET: 2/2 | WERI PART NO: DISCLAIMER | A4 | |
| REV | DATE | FILE | BY | | DRAW: QL | | | |