1	2	3	4	5		Ţ
24,4	9,4	2,6 ^{+0,05} 2,6 ^{+0,05} 1 1 22,6 ^{±0,05}	Ø 1,5 TECHNICAL CHARACTE MATERIAL INSULATOR: PA6/66 FLAMMABILITY RATING COLOR: GREEN CONTACT / PLATING: C ENVIRONMENTAL OPERATING TEMPERAT COMPLIANCE: LEAD FR ELECTRICAL	: UL94V0 OPPER ALLOY / Ni+Sn FURE: -30°C UP TO +120°C		/
0.5 ×1.2	3.5	PCB LAYOUT - COMPONEN		20 A 6,3 A 250 VAC 250 VAC GE: 1,5 KV 1,5 KV TANCE: 1,6 W o II :: 5/10 mΩ MAX 17 CAT. N°: PTF/77 2 TYPE: PTF/77 20 TYPE: PTF/77		
			SOLDERING JEDEC LEAD FREE WAY PACKAGING BOX	/E SOLDERING		
RoHS Compliant G F E D 14-MAR-17 CURRENT RA		GENERAL TOLERANCE - ±0,1				_
D 14-MAR-17 CORRENT RA C 30-JUN-15 SHOCKSAF B 01-APR-15 PROTECTION I A 11-SEP-14 PDF REV DATE FILE	E AK APPROVAL: FBr	SCALE:	DESCRIPTION: FUSEHOLDER BLOCKS - PC	B - CLIP COVER - THT - WR-FSH	SIZE	-

1	2	3	4	5	-
					_

А

В

С

Cautions and Warnings:

This electronic component is designed and developed with the intention for use

in general electronics equipments.

Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body, Wurth Elektronik must be asked for a written approval.

In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before by the user before usage.

R	toHS Compliant							
G				PROJECTION:	GENERAL TOLERANCE			1
F					.X = ⁺ /_ 0.2			
E					.XX = ⁺ /_ 0.15			
D						WÜRTH ELEKTRONIK		
С				APPROVAL: JC	UNIT: MM	DESCRIPTION: DISCLAIMER	SIZE	Ъ
В					SCALE:			Γ
Α	10-SEP-14	PDF	QL		SHEET: 2/2	WERI PART NO: DISCLAIMER	A4	
REV	DATE	FILE	BY		DRAW: QL			