


Dimensions: [mm]












Scale - 2:1

Product Marking:

Marking	4R7 (Inductance Code)
	iiii (iiiaastailes esas)

Recommended Hole Pattern: [mm]



Scale - 2:1

Certification:

Properties

Inductance

Rated Current

DC Resistance

Saturation Current

Electrical Properties:

RoHS Approval	Compliant [2011/65/EU&2015/863]					
REACh Approval	Conform or declared [(EC)1907/2006]					
Halogen Free	Conform [JEDEC JS709B]					
Halogen Free	Conform [IEC 61249-2-21]					

 R_{DC}

Test conditions

100 kHz/ 1 V

 $|\Delta L/L| < 30 \%$

 $\Delta T = 40 \text{ K}$

@ 20 °C

Value

4.7

8.7

13.5

8.5

Unit

mΩ

Tol.

±20%

max.

typ.

max.

Schematic:



General Properties:

Moisture Sensitivity Level (MSL)

REVISION

DATE (YYYY-MM-DD)

CHECKED

It is recommended that the temperature of the component does not exceed +125 °C under worst case conditions -40 °C up to +85 °C **Ambient Temperature Operating Temperature** -40 °C up to +125 °C Storage Conditions (in original < 40 °C; < 75 % RH packaging)

Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently

ROMS REACH HALOGEN	
WÜRTH	Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg


Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com

DaRu 001.002 2024-04-18 DIN ISO 2768-1m **WE-FAMI THT Power Inductor** ORDER CODE 744750420047 SIZE/TYPE BUSINESS UNIT STATUS PAGE 1280 Valid 1/8 eiSos


GENERAL TOLERANCE

MORE THAN


YOU EXPECT




Packaging Specification - Tray: [mm]




Packaging Specification - Inner Carton: [mm]



	L _{IC} (mm)	W _{IC} (mm)		No. of Tray (pcs.)	Qty. (pcs.)	Material
Tolerance	typ.	typ.	typ.			
Value	260.00	235.00	200.00	10	1000	Paper



Packaging Specification - Outer Carton: [mm]



	L _C (mm)	W _C (mm)	H _C (mm)	No. of Inner Carton (pcs.)	Qty. (pcs.)	Material
Tolerance	typ.	typ.	typ.			
Value	510.00	276.00	229 00	2	2000	Paner

RONS REACH HALOGEN COMPLIANT FREE		CHECKED DaRu	001.002	DATE (YYYY-MM-DD) 2024-04-18	GENERAL TOLERANCE DIN ISO 2768-1m	PROJECTION METHOD		-
		DESCRIPTION						
		WE-F/	WE-FAMI THT Power Inductor					
Würth Elektronik eiSos GmbH & Co. KG						ORDER CODE		
WÜRTH ELEKTRONIK MORE THAN YOU EXPECT EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com elSos@we-online.com				_	744750420	047		
	SIZE/TYPE			BUSINESS UNIT	STATUS		PAGE	
	1280			eiSos	Valid		4/8	

Classification Wave Soldering Profile:



Classification Wave Soldering Profile:

Profile Feature		Pb-Free Assembly	Sn-Pb Assembly		
Preheat Temperature Min	T _{s min}	100 °C	100 °C		
Preheat Temperature Typical	T _{s typical}	120 °C	120 °C		
Preheat Temperature Max T _{s n}		130 °C	130 °C		
Preheat Time t_s from T_{smin} to T_{smax}	t _s	70 seconds	70 seconds		
Ramp-up Rate △ T		150 °C max.	150 °C max.		
Peak Temperature		250 °C - 260 °C	235 °C - 260 °C		
Time of actual peak temperature	t _p	max. 10 seconds max. 5 seconds each wave	max. 10 seconds max. 5 seconds each wave		
Ramp-down Rate, Min		~ 2 K/ second	~ 2 K/ second		
Ramp-down Rate, Typical		~ 3.5 K/ second	~ 3.5 K/ second		
Ramp-down Rate, Max	·	~ 5 K/ second	~ 5 K/ second		
Time 25 °C to 25 °C		4 minutes	4 minutes		

refer to EN61760-1:2006

ROMERLANT COMMINION FIRE COMMINION F		CHECKED DaRu	REVISION 001.002	DATE (YYYY-MM-DD) 2024-04-18	GENERAL TOLERANCE DIN ISO 2768-1m	PROJEC METHOD		-
		DESCRIPTION WE-FA	MI THT	Power Ind	uctor	•		
Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-St. 1 74638 Waldenburg Comment	EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg					ORDER CODE 744750	420047	
MORE THAN YOU EXPECT	MORE THAN Tel. +49 (0) 79 42 945 - 0				BUSINESS UNIT eiSos	status Valid		PAGE 5/8

Further information Component Libraries: Altium_WE-FAMI (22c) Downloads_CADENCE_WE-FAMI (22a) Download_CadStar_WE-FAMI (19a) Eagle_WE-FAMI (20a) PSpice_WE-FAMI (22a) Spectre_WE-FAMI (23a) Free Sample Order: Order free samples of this article directly here! **Tutorials:** Single Coil Inductors (PDF) **REDEXPERT:** Calculate losses for 744750420047 in REDEXPERT



Cautions and Warnings:

The following conditions apply to all goods within the product series of WE-RIB LFS of Würth Elektronik eiSos GmbH & Co. KG:

General:

All recommendations according to the general technical specifications of the data sheet have to be complied with.

The usage and operation of the product within ambient conditions, which probably alloy or harm the wire isolation, has to be avoided.

If the product is potted in customer applications, the potting material might shrink during and after hardening. The product is exposed to the pressure of the potting material with the effect that the core, wire and termination is possibly damaged by this pressure and so the electrical as well as the mechanical characteristics are endangered to be affected. After the potting material is cured, the core, wire and termination of the product have to be checked if any reduced electrical or mechanical functions or destructions have occurred.

The responsibility for the applicability of customer specific products and use in a particular customer design is always within the authority of the customer. All technical specifications for standard products do also apply to customer specific products

Cleaning agents that are used to clean the customer application might damage or change the characteristics of the component, body, pins or termination.


Direct mechanical impact to the product shall be prevented as the ferrite material of the core could flake or in the worst case it could break.

Product specific:

Follow all instructions mentioned in the data sheet, especially:

- The soldering profile has to be complied with according to the technical wave soldering specification, otherwise this will void the
 warranty.
- All products shall be used before the end of the period of 12 months based on the product date code, if not a 100% solderability can't
 be ensured
- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- Strong forces and high accelerations of the components of the sizes 1014 and 8012 might have the effect of damaging the electrical
 connection or to harm the circuit board due to the heavy weight of the component. These damages will void the warranty.

The general and product specific cautions comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable; however, no responsibility is assumed for inaccuracies or incompleteness.



Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

