

MOLDED POWER INDUCTORS

WE-PMCI & WE-PMFI



more details online

744 792 621 47 L: 0.47 μ H R _{DC typ.} : 65 m Ω I _{SAT} : 3.35 A I _{RP} : 3.95 A	744 792 761 24 L: 0.24 μ H R _{DC typ.} : 17 m Ω I _{SAT} : 6.7 A I _{RP} : 6.9 A	744 792 871 47 L: 0.47 μ H R _{DC typ.} : 25 m Ω I _{SAT} : 7.4 A I _{RP} : 5.75 A	744 792 981 47 L: 0.47 μ H R _{DC typ.} : 18 m Ω I _{SAT} : 5.9 A I _{RP} : 7.3 A	744 793 201 651 10 L: 0.1 μ H R _{DC typ.} : 7.2 m Ω I _{SAT} : 13.7 A I _{RP} : 10.2 A	744 793 252 071 10 L: 0.1 μ H R _{DC typ.} : 5.6 m Ω I _{SAT} : 18.7 A I _{RP} : 12.3 A	744 793 322 571 10 L: 0.1 μ H R _{DC typ.} : 7.4 m Ω I _{SAT} : 21.5 A I _{RP} : 11.4 A	744 793 353 291 10 L: 0.1 μ H R _{DC typ.} : 4.8 m Ω I _{SAT} : 25 A I _{RP} : 16 A
744 792 622 10 L: 1 μ H R _{DC typ.} : 110 m Ω I _{SAT} : 2.6 A I _{RP} : 2.6 A	744 792 761 47 L: 0.47 μ H R _{DC typ.} : 256 m Ω I _{SAT} : 6.3 A I _{RP} : 5.4 A	744 792 872 10 L: 1 μ H R _{DC typ.} : 47 m Ω I _{SAT} : 5.1 A I _{RP} : 4.05 A	744 792 982 10 L: 1 μ H R _{DC typ.} : 44 m Ω I _{SAT} : 5.5 A I _{RP} : 4.95 A	744 793 201 651 47 L: 0.47 μ H R _{DC typ.} : 18.4 m Ω I _{SAT} : 7.5 A I _{RP} : 6.2 A	744 793 252 071 47 L: 0.47 μ H R _{DC typ.} : 11.3 m Ω I _{SAT} : 7.9 A I _{RP} : 9.3 A	744 793 322 571 47 L: 0.47 μ H R _{DC typ.} : 14.2 m Ω I _{SAT} : 10.6 A I _{RP} : 7.9 A	744 793 353 291 47 L: 0.47 μ H R _{DC typ.} : 12.7 m Ω I _{SAT} : 13.2 A I _{RP} : 9.9 A
744 792 751 47 L: 0.47 μ H R _{DC typ.} : 40 m Ω I _{SAT} : 5.15 A I _{RP} : 4.3 A	744 792 762 10 L: 1 μ H R _{DC typ.} : 55 m Ω I _{SAT} : 4.25 A I _{RP} : 3.15 A	744 792 872 22 L: 2.2 μ H R _{DC typ.} : 95 m Ω I _{SAT} : 3.1 A I _{RP} : 2.6 A	744 792 982 22 L: 2.2 μ H R _{DC typ.} : 89 m Ω I _{SAT} : 3.95 A I _{RP} : 3.35 A	744 793 201 652 10 L: 1 μ H R _{DC typ.} : 31.7 m Ω I _{SAT} : 5.25 A I _{RP} : 4.7 A	744 793 252 072 10 L: 1 μ H R _{DC typ.} : 23.8 m Ω I _{SAT} : 6.1 A I _{RP} : 6.1 A	744 793 322 572 10 L: 1 μ H R _{DC typ.} : 23.3 m Ω I _{SAT} : 9.15 A I _{RP} : 5.8 A	744 793 353 292 10 L: 1 μ H R _{DC typ.} : 18.4 m Ω I _{SAT} : 10.8 A I _{RP} : 7.3 A
744 792 752 10 L: 1 μ H R _{DC typ.} : 70 m Ω I _{SAT} : 3.45 A I _{RP} : 3.3 A	744 792 762 22 L: 2.2 μ H R _{DC typ.} : 130 m Ω I _{SAT} : 2.8 A I _{RP} : 2.1 A	744 792 881 47 L: 0.47 μ H R _{DC typ.} : 1 m Ω I _{SAT} : 7.9 A I _{RP} : 6.8 A	744 792 991 47 L: 0.47 μ H R _{DC typ.} : 18 m Ω I _{SAT} : 9.95 A I _{RP} : 7.1 A	744 793 201 652 47 L: 4.7 μ H R _{DC typ.} : 195 m Ω I _{SAT} : 2 A I _{RP} : 2.1 A	744 793 252 072 47 L: 4.7 μ H R _{DC typ.} : 114 m Ω I _{SAT} : 2.7 A I _{RP} : 2.75 A	744 793 322 572 47 L: 4.7 μ H R _{DC typ.} : 107 m Ω I _{SAT} : 4 A I _{RP} : 2.7 A	744 793 353 292 47 L: 4.7 μ H R _{DC typ.} : 63.2 m Ω I _{SAT} : 5.6 A I _{RP} : 3.85 A
744 792 752 22 L: 2.2 μ H R _{DC typ.} : 180 m Ω I _{SAT} : 2.4 A I _{RP} : 2 A		744 792 882 10 L: 1 μ H R _{DC typ.} : 40 m Ω I _{SAT} : 4.1 A I _{RP} : 4.6 A	744 792 992 10 L: 1 μ H R _{DC typ.} : 32 m Ω I _{SAT} : 6.95 A I _{RP} : 6.2 A				
		744 792 882 15 L: 1.5 μ H R _{DC typ.} : 71 m Ω I _{SAT} : 3.05 A I _{RP} : 3.2 A	744 792 992 22 L: 2.2 μ H R _{DC typ.} : 70 m Ω I _{SAT} : 4.8 A I _{RP} : 3.65 A				
		744 792 882 22 L: 2.2 μ H R _{DC typ.} : 80 m Ω I _{SAT} : 3.25 A I _{RP} : 3 A	744 792 901 25 L: 0.25 μ H R _{DC typ.} : 26 m Ω I _{SAT} : 15.65 A I _{RP} : 9.05 A				

WE-PMCI
Round Wire:

160808
201210
201610
252010
252012
322510
322512
322515

WE-PMFI
Flat Wire:

201610
252012
322512
353220

PASSIVE COMPONENTS | ELECTROMECHANICAL COMPONENTS | POWER MODULES | OPTOELECTRONICS | THERMAL MANAGEMENT | CUSTOM MAGNETICS | AUTOMOTIVE | WIRELESS CONNECTIVITY & SENSORS

Important information: Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on www.we-online.com for specifications. Würth Elektronik eiSos GmbH & Co. KG, EMC & Inductive Solutions. ©2025

ALL PRODUCTS
EX STOCK!