



# **Dimensions: [mm]**











# **Recommended Hole Pattern: [mm]**



Scale - 1:1

## Schematic:



# **Electrical Properties:**

Properties		Test conditions	Value	Unit	Tol.
Number of windings	N		2		
Inductance	L	10 kHz/ 0.1 mA	15	mH	+50%/-30%
Rated Current	I <sub>R</sub>	@ 70 °C	5	А	max.
DC Resistance	R <sub>DC</sub>	@ 20 °C	40	mΩ	max.
Rated Voltage	$V_R$	50 Hz	300	V (AC)	max.
Insulation Test Voltage		50 Hz/ 5 mA/ 2 sec.	2100	V (AC)	

## **Certification:**

RoHS Approval	Compliant [2011/65/EU&2015/863]
REACh Approval	Conform or declared [(EC)1907/2006]
ENEC 10 Approval	40048238
VDE Approval	40048238
Component Qualification	AEC-Q200 Grade 1

# **General Properties:**

CHECKED

HasA

REVISION

002.000

DATE (YYYY-MM-DD)

2024-01-26

Operating Temperature	-55 °C up to +125 °C					
Storage Conditions (in original packaging)	< 40 °C; < 75 % RH					
Moisture Sensitivity Level (MSL)	1					
Climatic Category	55/125/21					
Temperature Rise < 55 K						
Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently						






Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-St. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com GENERAL TOLERANCE


DIN ISO 2768-1m


PROJECTION METHOD

# **Typical Attenuation:**




# **Typical Impedance Characteristics:**






# **Test Setup:**


# According to CISPR 17




Network Analyzer: Keysight E5080A or equivalent

# **Derating Curve:**







# Packaging Specification - Tray and Carton: [mm]



L <sub>TRA</sub> (mm)	L1 <sub>TRA</sub> (mm)	L2 <sub>TRA</sub> (mm)	W <sub>TRA</sub> (mm)	W1 <sub>TRA</sub> (mm)	W2 <sub>TRA</sub> (mm)	H <sub>TRA</sub> (mm)	Packaging Unit	Material
typ.	typ.	typ.	typ.	typ.	typ.	typ.	pcs.	
235.00	170.00	42 50	185.00	130.00	32.50	24.00	25	Paner



L <sub>IC</sub> (mm)	W <sub>IC</sub> (mm)	H <sub>IC</sub> (mm)	L <sub>C</sub> (mm)	W <sub>C</sub> (mm)	H <sub>C</sub> (mm)	No. of tray	Packaging Unit	Material
typ.	typ.	typ.	typ.	typ.	typ.	pcs.	pcs.	
260	210	217	275.00	232.00	255.00	8	200	Paner



# **Classification Wave Soldering Profile:**



# **Classification Wave Soldering Profile:**

Profile Feature		Pb-Free Assembly	Sn-Pb Assembly			
Preheat Temperature Min	T <sub>s min</sub>	100 °C	100 °C			
Preheat Temperature Typical	T <sub>s typical</sub>	120 °C	120 °C			
Preheat Temperature Max	T <sub>s max</sub>	130 °C	130 °C			
Preheat Time $t_s$ from $T_{smin}$ to $T_{smax}$	t <sub>s</sub>	70 seconds	70 seconds			
Ramp-up Rate	ΔΤ	150 °C max.	150 °C max.			
Peak Temperature	T <sub>p</sub>	250 °C - 260 °C	235 °C - 260 °C			
Time of actual peak temperature	t <sub>p</sub>	max. 10 seconds max. 5 seconds each wave	max. 10 seconds max. 5 seconds each wave			
Ramp-down Rate, Min		~ 2 K/ second	~ 2 K/ second			
Ramp-down Rate, Typical		~ 3.5 K/ second	~ 3.5 K/ second			
Ramp-down Rate, Max		~ 5 K/ second	~ 5 K/ second			
Time 25 °C to 25 °C		4 minutes	4 minutes			

refer to EN61760-1:2006

	DYE AEC 0200		CHECKED HasA	REVISION 002.000	DATE (YYYY-MM-DD) 2024-01-26	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD		<b>)</b> -
RoHS COMPLIANT COMPLIANT	WÜRTH	125 °C  Würth Elektronik eiSos GmbH & Co. KG  EMC & Inductive Solutions  Max-Eyth-Str. 1  74638 Wäldenburg	WE-CMBNC Common Mode Power Line Choke Nanocrystalline				ORDER CODE 7448040515			
WE	MORE THAN YOU EXPECT	Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com elSos@we-online.com	SIZE/TYPE L			BUSINESS UNIT eiSos	status Valid		1	PAGE 5/8

## **Further information**

# **Component Libraries:**



3D\_WE-CMBNC-L\_7448040515



Altium\_WE-CMBNC (22b)



Downloads\_CADENCE\_WE-CMBNC (21a)



Cadstar\_WE-CMBNC (20a)



Eagle\_WE-CMBNC (20a)



Download\_IGS\_7448040515



PSpice\_WE-CMBNC (22a)



S-Parameter\_7448040515 (20a)



Download\_STP\_7448040515

# **Design Kits:**

Design Kit WE-CMB / WE-ExB / WE-CMBNC Common Mode Power Line Chokes

## Free Sample Order:

Order free samples of this article directly here!

### **Tutorials:**

- Applications of EMC Components (PDF)
- Behaviour of Common Mode Chokes (PDF)

## **REDEXPERT:**

Find the right Common Mode Choke with REDEXPERT





Würth Elektronik eiSos GmbH & Co. KG EMc & Inductive Solutions Max-Eyth-St. 1 7 44638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com CHECKED

HasA

REVISION

002.000

DATE (YYYY-MM-DD)

2024-01-26

DESCRIPTION

WE-CMBNC Common Mode Power

Line Choke Nanocrystalline

ORDER CODE

7448040515

SZE/TYPE

BUSINESS LINT
EISOS

Valid

PAGE
6/8

GENERAL TOLERANCE

DIN ISO 2768-1m

PROJECTION METHOD

# **Cautions and Warnings:**

# The following conditions apply to all goods within the product series of WE-CMBNC of Würth Elektronik eiSos GmbH & Co. KG:

#### General:

- This electronic component is designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
  equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
  ship control), transportation signal, disaster prevention, medical, public information network, etc. where higher safety and reliability are
  especially required and/or if there is the possibility of direct damage or human injury.
- Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions
  specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
  Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
  sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the
  authority of the customer. All technical specifications for standard products also apply to customer specific products.

## **Product specific:**

### Soldering

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- · All other soldering methods are at the customers' own risk.

### **Cleaning and Washing:**

Washing agents used during the production to clean the customer application might damage or change the characteristics of the wire
insulation, marking or plating. Washing agents may have a negative effect on the long-term functionality of the product.

### Potting

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the core. Expansion could damage the component. We recommend a
manual inspection after potting to avoid these effects.

## **Storage Conditions:**

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer
  degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of
  shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.


## Packaging:

 The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

### **Handling:**

- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- Applying currents with audio-frequency signals may result in audible noise due to the magnetostrictive material properties.
- Due to heavy weight of the components, strong forces and high accelerations may have the effect to damage the electrical connection
  or to harm the circuit board and will void the warranty.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness



# **Important Notes**

# The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

## 1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

## 2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

#### 3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

### 4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

### 5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

## 6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

## 7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

### 8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

