




# **Dimensions: [mm]**












Unless otherwise defined tolerance: ±0,25mm


**Recommended Land Pattern: [mm]** 



Unless otherwise defined tolerance: ±0,10mm no vias or traces underneath the component

Scale - 3:1

## **Schematic:**



## **Product Marking:**

Pin 1	•
Marking	7490100161A YYWW



Scale - 3:1

# **Electrical Properties:**

Properties		Test conditions	Value	Unit	Tol.				
Inductance	L	100 kHz / 100 mV @ 8 mA DC bias	350	μН	min.				
Insulation Test Voltage $V_T$		1 min.	1500	V (RMS)	min.				
Insertion Loss	Insertion Loss		-1.1	dB	max.				
Return Loss	RL	1-30 MHz @ 100 Ω	-18	dB	min.				
Return Loss	RL	30-60 MHz @ 100 Ω	-14	dB	min.				
Return Loss	RL	60-80 MHz @ 100 Ω	-12	dB	min.				
Return Loss	RL	80-100 MHz @ 100 Ω	-10	dB	min.				
Differential to Common Mode Rejection Ratio		1-30 MHz	-38	dB	min.				
Differential to Common Mode Rejection Ratio	DCMR	30-60 MHz	-38	dB	min.				
Differential to Common Mode Rejection Ratio	DCMR	60-100 MHz	-30	dB	min.				
Crosstalk	CT	1-60 MHz	-40	dB	min.				
Crosstalk	CT	60-100 MHz	-35	dB	min.				
Turns Ratio	n		1:1		±3%				
Data rate		10/100BASE-TX							

# **General Information:**

It is recommended that the temperature of the component does not exceed +125 °C under worst case conditions							
Operating Temperature -40 °C up to +125 °C							
Storage Conditions (in original packaging)	< 40 °C; < 75 % RH						
Moisture Sensitivity Level (MSL)							
Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently							

# **Certification:**


RoHS Approval	Compliant [2011/65/EU&2015/863]
none ripprovai	5011pilant [2011/00/2002010/000]


# **Certification:**


REACh Approval	Conform or declared [(EC)1907/2006]
cURus Approval	E472316 [UL 62368-1]

MORE THAN YOU EXPECT	Geritairy Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com				BUSINESS UNIT eiSos	status Valid		PAGE 2/8
WURTH ELEKTRONIE	Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany		former	UU DASE-I	A SIVII	ORDER COD 749	0100161A	
ROHS REACH COMPLIANT	RoHS REACh			00 Base-T	VCMT			
CALUS		JefL	003.000	2024-04-11	DIN ISO 2768-1m		METHOD HAND	<b>\Phi</b> -

# Packaging Specification - Tape: [mm]









Packaging is refered to the international standard IEC 60286-3:2013


Таре Туре	A0 (mm)	B0 (mm)	W (mm)	T (mm)	T1 (mm)	T2 (mm)	KO (mm)	P0 (mm)	P1 (mm)	P2 (mm)	DO (mm)	D1 (mm)	E1 (mm)	E2 (mm)	F (mm)	Material	Qty. (pcs.)
	typ.	typ.	+0,3/ -0,1	ref.	max.	typ.	typ.	±0,1	±0,1	±0,1	+0,1/-0,0	min.	±0,1	min.	±0,1		
2a	10.50	13,00	24,00	0,40	0,10	6,30	5,90	4,00	16,00	2,00	1,50	1,50	1,75	22,25	11,50	Polystyrene	600

# Packaging Specification - Reel: [mm]





	A (mm)	B (mm)	C (mm)	D (mm)	N (mm)	W1 (mm)	W2 (mm)	W3 (mm)	W3 (mm)	Material
Tolerance	± 2,0	min.	min.	min.	min.	+ 2,0	max.	min.	max.	
Value	330,00	1,50	12,80	20,20	60,00	24,40	30,40	23,90	27,40	Polystyrene



Pull-off force Tape width 24 mm





Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg

Germany Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com

GENERAL TOLERANCE REVISION DATE (YYYY-MM-DD) 003.000 2024-04-11

CHECKED

JefL

DIN ISO 2768-1m

PROJECTION METHOD

WE-LAN 10/100 Base-TX SMT **Transformer** 


7490100161A

STATUS BUSINESS UNIT PAGE eiSos Valid 3/8

ORDER CODE


This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment where a higher safety standard and reliability standard is especially required or where a failure of the product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik eiSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component within its used in electrical circuits that require high safety and reliability evaluation checks for safety must be performed on every electronic component within its used in electrical circuits that require high safety and reliability the control and reliability evaluation checks for safety must be performed on every electronic component within its used in electrical circuits that require high safety and reliability evaluation checks for safety must be performed on every electronic component within its used in electrical circuits that require high safety and reliability the control or performed about the intent of such usage before the design-in stage. In addition, sufficient reliability and reliability that and the product is not authorized for use in equipment where a failure of the product is reasonably expected to cause severe personal injury or death, unless that particularly expected to cause evere personal injury or death, unless the particular expectation of the product is reasonably expected to cause evere personal injury or death, unless that particularly expected to cause evere personal injury or death, unless the particular expectation of the product is reasonable to cause every expected to cause

# Packaging Specification - Inner Carton: [mm]



		L <sub>IC</sub> (mm)	W <sub>IC</sub> (mm)	H <sub>IC</sub> (mm)	No. of Reel (pcs.)	Qty. (pcs.)	Material
Tole	rance	typ.	typ.	typ.			
Valu	le.	35.00	345 00	335 00	1	600	Paner

# Packaging Specification - Outer Carton: [mm]



	L <sub>C</sub> (mm)	W <sub>C</sub> (mm)	H <sub>C</sub> (mm)	No. of Inner Carton (pcs.)	Qty. (pcs.)	Material
Tolerance	typ.	typ.	typ.			
Value	400	370	370	10	6000	Paper

C CAN'US		JefL JefL	REVISION 003.000	DATE (YYYY-MM-DD) 2024-04-11	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	<b>-</b>
ROHS REACH COMPLIANT COMPLIANT		WE-LAN 10/100 Base-TX SMT						·
WURTH ELEKTRONIK	Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany	Transf	ormer			749	0100161A	
MORE THAN YOU EXPECT	Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com				BUSINESS UNIT eiSos	status Valid		PAGE 4/8

# **Classification Reflow Profile for SMT components:**



# **Classification Reflow Soldering Profile:**

Profile Feature		Value
Preheat Temperature Min	T <sub>s min</sub>	150 °C
Preheat Temperature Max	T <sub>s max</sub>	200 °C
Preheat Time $t_s$ from $T_{s  min}$ to $T_{s  max}$	t <sub>s</sub>	60 - 120 seconds
Ramp-up Rate (T <sub>L</sub> to T <sub>P</sub> )		3 °C/ second max.
Liquidous Temperature	T <sub>L</sub>	217 °C
Time t <sub>L</sub> maintained above T <sub>L</sub>	t <sub>L</sub>	60 - 150 seconds
Peak package body temperature	T <sub>p</sub>	$T_p \le T_c$ , see Table below
Time within 5°C of actual peak temperature	t <sub>p</sub>	20 - 30 seconds
Ramp-down Rate (T <sub>P</sub> to T <sub>L</sub> )		6 °C/ second max.
Time 25°C to peak temperature		8 minutes max.

refer to IPC/ JEDEC J-STD-020E

# Package Classification Reflow Temperature (T<sub>c</sub>):

Properties	Volume mm³ <350	Volume mm <sup>3</sup> 350-2000	Volume mm³ >2000
PB-Free Assembly I Package Thickness < 1.6 mm	260 °C	260 °C	260 °C
PB-Free Assembly   Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C
PB-Free Assembly   Package Thickness > 2.5 mm	250 °C	245 °C	245 °C

refer to IPC/ JEDEC J-STD-020E

CAL US		JefL	003.000	DATE (YYYY-MM-DD) 2024-04-11	GENERAL TOLERANCE DIN ISO 2768-1m		PROJECTION METHOD	<del>]</del>	
ROHS COMPLIANT  REACH COMPLIANT  WURTH ELEKTRONIK  WURTH ELEKTRONIK  WURTH ELEKTRONIK  WURTH ELEKTRONIK  RAS-Eyn-St. 1  7-4638 Waldenburg		l l	WE-LAN 10/100 Base-TX SMT Transformer				ORDER CODE 7490100161A		
MORE THAN YOU EXPECT	HAN Tel. +49 (0) 79 42 945 - 0				BUSINESS UNIT eiSos	status Valid		5/8	

## **Further information**

## **Component Libraries:**



Altium WE-LAN (22b)



Downloads\_CADENCE\_WE-LAN (24a)



Cadstar\_WE-LAN (20a)



Eagle\_WE-LAN (24a)



Download\_IGS\_7490100161A



PSpice\_WE-LAN (23a)



S-Parameter\_7490100161A (20a)



Download\_STP\_7490100161A

## Free Sample Order:

Order free samples of this article directly here!


## **Tutorials:**

- High Performance Low EMI Series (PDF)
- The LAN-PoE Connection (PDF)
- Connecting LAN Transformers (PDF)

High Voltage LAN Transformers (PDF)

## **REDEXPERT:**

Calculate losses for 7490100161A in REDEXPERT



# **Cautions and Warnings:**

# The following conditions apply to all goods within the product series of WE-LAN of Würth Elektronik eiSos GmbH & Co. KG:

#### General:

- This electronic component is designed and developed with the intention for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
  equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
  ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are
  especially required and/or if there is the possibility of direct damage or human injury.
- Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions
  specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
  Elektronik does not guarantee any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
  sustainability over time.
- The customer is responsible for the functionality of their own products. All technical specifications for standard products also apply to customer specific products.

## **Product specific:**

## Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- · All other soldering methods are at the customers' own risk.
- Strong forces which may affect the coplanarity of the components' electrical connection with the PCB (i.e. pins), can damage the part, resulting in a void of the warranty.

## **Cleaning and Washing:**

- Washing agents used during the production to clean the customer application might damage or change the characteristics of the wire
  insulation, marking or plating. Washing agents may have a negative effect on the long-term functionality of the product.
- Using a brush during the cleaning process could break the wire due to its small diameter. Therefore, we do not recommend using a
  brush during the PCB cleaning process.

## Potting:

If the product is potted in the costumer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the core. Expansion could damage the components. We recommend a
manual inspection after potting to avoid these effects.

## **Storage Conditions:**

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer
  degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of
  shipment.
- · Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.


## Packaging:

 The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

#### **Handling:**

- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- Applying currents with audio-frequency signals might result in audible noise due to the magnetostrictive material properties.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.



# **Important Notes**

# The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

#### 1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

## 2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

#### 3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

#### 4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

#### 5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

## 6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

## 7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

#### 8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

