Kunde / customer :

Artikelnummer / part number : 74841224

748412245




size




Bezeichnung : SMD-Balun WE-BAL description : Chip-Balun WE-BAL

**DATUM / DATE : 2004-12-14** 

### A Mechanische Abmessungen / dimensions:





Α	1,6 ± 0,1	mm
В	$0.8 \pm 0.1$	mm
С	0,6 ± 0,1	mm
а	0,2 ± 0,1	mm
b	0,2 + 0,1/-0,2	mm
С	0,15 ± 0,1	mm
d	0,3 ± 0,1	mm
е	$0.5 \pm 0.05$	mm

0603

## B Elektrische Eigenschaften / electrical properties:

### C Abbildung/ apperance:

5						
Eigenschaften / properties	Testbedingungen / test conditions		Wert / value	Einheit / unit	tol.	
Frequenzbereich/		f	2400 2500	MHz		
frequency range		•	2400 2000	1711 12		
Einfügedämpfung/ insertion loss	2400 2500 MHz		2,0	dB	max.	
Einfügedämpfung/ insertion loss	2400 2500 MHz		1,20	dB	typ.	
VSWR/	2400 2500 MHz		2,0		max.	
VSWR	2400 2500 WII IZ		2,0		IIIax.	
Phasendifferenz/			180	0	± 10°	
phase imbalance			100		± 10	
Amplitudendifferenz/			2,0	dB	max.	
amplitude imbalance			2,0	GD	max.	
Eingangsimpedanz/		7	50	Ω	typ.	
unbalanced impedance			30	5.2	typ.	
Ausgangsimpedanz/		Ζ	50	0	tvn	
balanced impedance		_	30	Ω	typ.	
Leistung/		Р	2	W	may	
power capacity		٢	2	۷V	max.	



#### D Prüfgeräte / test equipment:

#### E Testbedingungen / test conditions:

Network Analyzer Agilent E5071B

Luftfeuchtigkeit / humidity:

50 ~ 70%

Umgebungstemperatur / temperature: 20°C ~ 25°C

#### F Werkstoffe & Zulassungen / material & approvals

#### G Eigenschaften / general specifications:

Basismaterial / base material:

Keramik / ceramic

Betriebstemp. / operating temperature:  $-40^{\circ}\text{C} - +85^{\circ}\text{C}$ 

Kontaktmaterial / contact plating: AG + Ni + Sn

Lagerbedingungen / storage conditions:  $5^{\circ}\text{C} \sim 35^{\circ}\text{C}$ 

45 ~ 75% RH

Freignbe artailt / general relegae:	Kunde / customer			
Freigabe erteilt / general release:				
Datum / date	Unterschrift / signature			
	Würth Elektronik			
		00	Version 1	09-03-01
Geprüft / checked	Kontrolliert / approved	Name	Änderung / modification	Datum/date

#### Würth Elektronik eiSos GmbH & Co.KG

Kunde / customer :

Artikelnummer / part number : 748412245


Bezeichnung : SMD-Balun WE-BAL description : Chip-Balun WE-BAL





**DATUM / DATE : 2004-12-14** 

#### H Lötpadempfehlung / solder pads:




\* Line width should be designed to provide proper impedance matching characteristics, depending on PCB material and thickness.




Through-hole (Ø 0.3)

Units: mm

### K Messdiagramme/ measuring diagrams:



\* Impedance for ports 2 and 3 = ½ (Balanced Impedance)



No.	Terminal Name	No.	Terminal Name		
1	Unbalanced Port (IN)	4	Balanced Port (OUT 2)		
2	GND	5	GND		
(3)	Balanced Port (OUT 1)	6	NC		

#### Würth Elektronik eiSos GmbH & Co.KG

Kunde / customer :

Artikelnummer / part number : 748412245

Bezeichnung : SMD-Balun WE-BAL description : Chip-Balun WE-BAL






**DATUM / DATE : 2004-12-14** 


#### L Messdiagramme / measuring diagrams:

#### Insertion Loss (dB) / Return Loss (dB)



## Frequency [GHz]

#### Amplitude Balance (dB) / Phase Balance (degree)



## Frequency [GHz]

#### Würth Elektronik eiSos GmbH & Co.KG

This electronic component has been designed and developed for usage in general electronic equipment. Before incorporating this component into any equipment where higher safety and reliability is especially required or if there is the possibility of direct damage or injury to human body, for example in the range of aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc, Würth Elektronik eiSos GmbH must be informed before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

Kunde / customer :

Artikelnummer / part number : 748412245








**DATUM / DATE : 2004-12-14** 


WÜRTH ELEKTRONIK

Bezeichnung : SMD-Balun WE-BAL description : Chip-Balun WE-BAL

## I Rollenspezifikation / tape and reel specification :





	Gurtspezifikation / Tape specification:					
	Α	0,95 ± 0,1	mm			
	В	4,0 ± 0,1	mm			
	C	$8,0 \pm 0,2$	mm			
	D	1,5 +0,1/-0,0	mm			
	Е	4,0 ± 0,1	mm			
	F	$2,0 \pm 0,05$	mm			
	G	1,75 ± 0,1	mm			
	Η	3,5 ± 0,1	mm			
		1,8 ± 0,1	mm			
	J	0,85 max.	mm			
	Т	$0,2 \pm 0,05$	mm			



Rollenspezifikation / Reel specification:			
а	178,0 ± 2,0	mm	
b	13,0 ± 0,3	mm	
С	21,8 ± 0,8	mm	
d	$2,0 \pm 0,5$	mm	
е	60,0 ± 0,5	mm	
f	1,2 ± 2,0	mm	
g	$9.0 \pm 0.3$	mm	

The force for tearing off cover tape is 10 to 130 grams in arrow direction





Eroigaba artailt / gaparal ralagas:	Kunde / customer		_	
Freigabe erteilt / general release:				
Datum / date	Unterschrift / signature			
	Würth Elektronik			
·				
		AWe	Version 1	04-10-11
Geprüft / checked	Kontrolliert / approved	Name	Änderung / modification	Datum/dat

Würth Elektronik eiSos GmbH & Co.KG

D-74638 Waldenburg · Max-Eyth-Str. 1 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400 http://www.we-online.de