


# Design Kit LAN Transformers & WERI Connectors



<p><b>10/100BT</b></p> <p><b>749 010 012 A</b></p> <p>Op. Temp.: 0°C to +70°C</p> <p>No. of Ports: 1</p> <p>HiPot Test: 1.5 kV</p>	<p><b>10/100/1000BT Low Profile</b></p> <p><b>749 020 111 A</b></p> <p>Op. Temp.: 0°C to +70°C</p> <p>No. of Ports: 1</p> <p>HiPot Test: 1.5 kV</p>	<p><b>10/100BT PoE+</b></p> <p><b>749 012 011 0</b></p> <p>Op. Temp.: -40°C to +85°C</p> <p>No. of Ports: 1</p> <p>HiPot Test: 1.5 kV</p>	<p><b>10/100/1000BT PoE</b></p> <p><b>749 023 010 A</b></p> <p>Op. Temp.: 0°C to +70°C</p> <p>No. of Ports: 1</p> <p>HiPot Test: 1.5 kV</p>	<p><b>10/100BT</b></p> <p><b>749 010 040 1</b></p> <p>Op. Temp.: -40°C to +85°C</p> <p>No. of Ports: 4</p> <p>HiPot Test: 1.5 kV</p>
<p><b>10/100/1000BT HPLE</b></p> <p><b>749 023 015</b></p> <p>Op. Temp.: 0°C to +70°C</p> <p>No. of Ports: 1</p> <p>HiPot Test: 1.5 kV</p>	<p><b>10/100/1000BT High Voltage</b></p> <p><b>749 024 012</b></p> <p>Op. Temp.: -40°C to +85°C</p> <p>No. of Ports: 1</p> <p>HiPot Test: 4 kV</p>	<p><b>8P8C Horiz. Shielded 1 port</b></p> <p><b>615 008 14X XXX</b></p> <p>Op. Temp.: -40°C to +85°C</p> <p>No. of Ports: 1</p> <p>HiPot Test: n.A.</p>	<p><b>8P8C Horiz. Shielded 2 ports</b></p> <p><b>615 016 137 XXX / 615 016 24X XXX</b></p> <p>Op. Temp.: -40°C to +85°C</p> <p>No. of Ports: 2</p> <p>HiPot Test: n.A.</p>	<p><b>8P8C Horiz. Plastic 1x4</b></p> <p><b>615 032 137 XXX</b></p> <p>Op. Temp.: -40°C to +85°C</p> <p>No. of Ports: 4</p> <p>HiPot Test: n.A.</p>
<p><b>8P8C Horiz. Shielded 2x2</b></p> <p><b>615 032 243 321</b></p> <p>Op. Temp.: -40°C to +85°C</p> <p>No. of Ports: 4</p> <p>HiPot Test: n.A.</p>	<p><b>8P8C Horiz. Shielded dual USB</b></p> <p><b>615 016 338 621</b></p> <p>Op. Temp.: -25°C to +85°C</p> <p>No. of Ports: 1</p> <p>HiPot Test: n.A.</p>	<p><b>8P8C/10P8C Horiz. Shielded/ Plastic 1 port</b></p> <p><b>634 008 1XX XXX / 635 108 1XX XXX</b></p> <p>Op. Temp.: -40°C to +85°C</p> <p>No. of Ports: 1</p> <p>HiPot Test: n.A.</p>	<p><b>8P8C Vert. THT/SMD 1 port</b></p> <p><b>615 008 1XX XXX</b></p> <p>Op. Temp.: -40°C to +85°C</p> <p>No. of Ports: 1</p> <p>HiPot Test: n.A.</p>	<p><b>8P8C 45° Entry Shielded/ Plastic 1 port</b></p> <p><b>615 008 145 XXX</b></p> <p>Op. Temp.: -40°C to +85°C</p> <p>No. of Ports: 1</p> <p>HiPot Test: n.A.</p>

EMC COMPONENTS | INDUCTORS | **TRANSFORMERS** | RF COMPONENTS | CIRCUIT PROTECTION | EMC SHIELDING MATERIAL | LEDs | **CONNECTORS** | SWITCHES | ASSEMBLY TECHNIQUE | POWER ELEMENTS

**Important information:** Würth Elektronik's design kits contain reference components. These components correspond with the current product development status on the day of supply. Exchange of the reference components to components with up-to-date product development status is not carried out automatically. No liability is taken for the use of these reference components. Therefore, please request new samples prior to releases for series production and product release.

Please check datasheets on [www.we-online.com](http://www.we-online.com) for specifications. Würth Elektronik eiSos GmbH & Co. KG, EMC & Inductive Solutions. © 2015

[www.we-online.com](http://www.we-online.com)

**All products  
in stock!**