




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn96% Ag4%	Yes	Yes

6B



TERM. NO.'s FOR REF. ONLY



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
INDUCTANCE	23-22 100kHz, 100mVAC, 8mADC, Lp	350uH min.
INDUCTANCE	20-19 100kHz, 100mVAC, 8mADC, Lp	350uH min.
INDUCTANCE	17-16 100kHz, 100mVAC, 8mADC, Lp	350uH min.
INDUCTANCE	14-13 100kHz, 100mVAC, 8mADC, Lp	350uH min.
DIELECTRIC	1-24 tie(1+4+7+10, 15+18+21+24) 1800Vrms, 1 second	1500Vrms, 1 minute
INSERTION LOSS	300k - 125MHz	-1.2dB max.
RETURN LOSS	500kHz - 40MHz	-18dB min.
RETURN LOSS	40M - 60MHz	-15dB min.
RETURN LOSS	60M - 80MHz	-12dB min.
RETURN LOSS	80M - 100MHz	-10dB min.
CROSSTALK	300kHz - 100MHz	-35dB min.
CMRR	300k - 32MHz	-42dB min.
CMRR	32M - 100MHz	-33dB min.

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: 0°C to +70°C.

COPLANARITY: All 24 terminals must lie on a plane within .004 [.10] of Surface A after lead tinning.

Designed to handle 350mADC and meet 802.3af.

REV.	DATE
6B	2/10
6A	2/08

Packaging Specifications Method: Tape & Reel PKG-0653 www.midcom-inc.com	Tolerances unless otherwise specified: Angles: ±1° Decimals: ±.005 [.13] Fractions: ±1/64 Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER Gigabit & PoE eiSos p/n: 749023016	 www.midcom-inc.com	DRAWING NO. 749023016	
	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.			REVISIONS: SEE SHEET 1	SCALE ---