



CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn98%, Cu2%	Yes	Yes





TERM. NO.'s FOR REF. ONLY



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:

PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-8 @20°C	0.7 ohms max.
D.C. RESISTANCE	4-5 @20°C	0.7 ohms max.
INDUCTANCE	1-8 100kHz, 10mVAC, Ls	1.2mH min.
INDUCTANCE	4-5 100kHz, 10mVAC, Ls	1.2mH min.
DIELECTRIC	ALL WINDINGS 5000VAC, 2 seconds	-
URNS RATIO	(1-8):(4-5)	1:1, ±1%



GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +85°C.

VOLT RATING: 27.2 Vusec.

BASIC INSULATION: 1.4mm Creepage & Clearance.

Wire insulation & RoHS status not affected by wire color.
Wire insulation color may vary depending on availability.

DETAILS SUBJECT TO CHANGE

REV.	DATE	Packaging Specifications Method: Tape & Reel PKG-0576 www.we-online.com/midcom		Tolerances unless otherwise specified: Angles: ±1° Fractions: ±1/64 Decimals: ±.005 [.13] Footprint: ±.005 [.13]	DRAWING TITLE TRANSFORMER	PART NO. 750311765
6B	3/19	SEE REVISION SHEET FOR REVISION LEVEL	CONVENTION PLACEMENT	This drawing is dual dimensioned. Dimensions in brackets are in millimeters.	eiSos p/n: 750311765	
6A	4/13					SPECIFICATION SHEET 1 OF 1