




CUSTOMER TERMINAL	RoHS	LEAD(Pb)-FREE
Sn98%, Cu2%	Yes	Yes

more than you expect



ELECTRICAL SPECIFICATIONS @ 25°C unless otherwise noted:


PARAMETER	TEST CONDITIONS	VALUE
D.C. RESISTANCE	1-2 @20°C	0.040 ohms max.
D.C. RESISTANCE	4-3 @20°C	0.040 ohms max.
INDUCTANCE	1-2 10kHz, 100mVAC, Ls	9mH ±35%
INDUCTANCE	4-3 10kHz, 100mVAC, Ls	9mH ±35%
DIELECTRIC	1-4 600VAC, 1 second	500VAC, 1 minute

GENERAL SPECIFICATIONS:

OPERATING TEMPERATURE RANGE: -40°C to +85°C.

CURRENT RATING: 6ADC

REV.	DATE	Packaging Specifications
6C	12/19	Method: Tray PKG-0667 www.we-online.com/midcom
6B	9/16	
6A	11/11	SEE REVISION SHEET FOR REVISION LEVEL



Tolerances unless otherwise specified:
Angles: $\pm 1^\circ$ Decimals: $\pm .005$ [.13]
Fractions: $\pm 1/64$ Footprint: $\pm .001$ [.03]

This drawing is dual dimensioned. Dimensions in brackets are in millimeters.

DRAWING TITLE

INDUCTOR

eiSos p/n: 750311795



PART NO.

750311795

SPECIFICATION SHEET 1 OF 1